











Type	Gate			Gate			Gate			Gate			Gate			
																
Fig	<b>10-DSR-N</b>			<b>10-DSRF-N</b>			<b>10-DSRF-N(BB)</b>			<b>16-DSR-N</b>			<b>16-DSRF-N</b>			
Product Code	<b>602A</b>			<b>612A</b>			<b>613A</b>			<b>622A</b>			<b>632A</b>			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
1/2	15	60	150	60	90	164	70				65	163	70	108	163	70
3/4	20	70	171	70	100	165	70				75	182	80	117	164	70
1	25	75	198	80	110	188	80				80	212	90	127	187	80
1 1/4	32	85	233	90	120	219	90				90	245	100	140	219	90
1 1/2	40	95	274	100	130	253	100				100	285	115	165	253	100
2	50	105	318	115	140	285	115	178	352	200	110	330	135	178	285	115
2 1/2	65							190	410	200						
3	80							203	479	250						
4	100							229	566	250						
5	125							254	667	300						
6	150							267	779	300						
8	200							292	969	350						
10	250							330	1181	400						
12	300							356	1404	450						
Body	Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
Bonnet/Cap/Cover	Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
Stem	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Disc	Stainless Steel			Stainless Steel						Stainless Steel						
Note	Screwed ends			Screwed ends						Screwed ends						

Type	Gate			Gate			Gate			Gate			Globe			
																
Fig	<b>16-DSRF-N(BB)</b>			<b>20-DSR-N</b>			<b>20-DSRF-N</b>			<b>20-DSRF-N(BB)</b>			<b>10-DG-N</b>			
Product Code	<b>633</b>			<b>642A</b>			<b>652A</b>			<b>653A</b>			<b>600A</b>			
inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
1/4	8													50	108	60
3/8	10													55	108	60
1/2	15				70	175	90	108	175	90				65	122	70
3/4	20				75	177	90	117	177	90				80	125	80
1	25				85	214	100	127	214	100				90	146	90
1 1/4	32				95	241	115	140	241	115				105	160	100
1 1/2	40				105	277	135	165	277	135				120	180	115
2	50	178	352	200	115	301	135				216	395	200	140	198	135
2 1/2	65	190	410	200							241	450	200			
3	80	203	479	250							283	520	250			
4	100	229	566	250							305	595	250			
5	125	254	667	300							381	725	300			
6	150	267	779	300							403	820	350			
8	200	292	993	350							419	1070	400			
10	250	330	1181	400							457	1247	450			
12	300	356	1404	450							502	1451	500			
Body	Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
Bonnet/Cap/Cover	Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
Stem	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Body Seat	Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
Note				Screwed ends									Screwed ends			