

# High Temperature Silicone Foam

## Silicone Foam

Silicone displays excellent resistance to high and low temperatures, compression set, chemicals and weather. Applications include gaskets, heat shields, fire stops, cushions, and insulation for a wide variety of applications.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture	Specs Met
ZUSA731AMFS-128	Strip	Closed Cell	Silicone	Standard	1/16"	1/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-130	Strip	Closed Cell	Silicone	Standard	1/16"	3/16"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-2	Strip	Closed Cell	Silicone	Standard	1/16"	1/4"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-6	Strip	Closed Cell	Silicone	Standard	1/16"	1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-101	Strip	Closed Cell	Silicone	Standard	1/16"	5/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-108	Strip	Closed Cell	Silicone	Standard	1/16"	3/4"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-116	Strip	Closed Cell	Silicone	Standard	1/16"	7/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-12	Strip	Closed Cell	Silicone	Standard	1/16"	1"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-18	Strip	Closed Cell	Silicone	Standard	1/16"	1 1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-24	Strip	Closed Cell	Silicone	Standard	1/16"	2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-30	Strip	Closed Cell	Silicone	Standard	1/16"	2 1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-36	Strip	Closed Cell	Silicone	Standard	1/16"	3"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-129	Strip	Closed Cell	Silicone	Standard	1/8"	1/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-131	Strip	Closed Cell	Silicone	Standard	1/8"	3/16"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-1	Strip	Closed Cell	Silicone	Standard	1/8"	1/4"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-5	Strip	Closed Cell	Silicone	Standard	1/8"	1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-102	Strip	Closed Cell	Silicone	Standard	1/8"	5/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-109	Strip	Closed Cell	Silicone	Standard	1/8"	3/4"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-117	Strip	Closed Cell	Silicone	Standard	1/8"	7/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-11	Strip	Closed Cell	Silicone	Standard	1/8"	1"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-17	Strip	Closed Cell	Silicone	Standard	1/8"	1 1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-23	Strip	Closed Cell	Silicone	Standard	1/8"	2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-29	Strip	Closed Cell	Silicone	Standard	1/8"	2 1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-35	Strip	Closed Cell	Silicone	Standard	1/8"	3"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-132	Strip	Closed Cell	Silicone	Standard	3/16"	3/16"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-3	Strip	Closed Cell	Silicone	Standard	3/16"	1/4"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-7	Strip	Closed Cell	Silicone	Standard	3/16"	1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-103	Strip	Closed Cell	Silicone	Standard	3/16"	5/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-110	Strip	Closed Cell	Silicone	Standard	3/16"	3/4"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-118	Strip	Closed Cell	Silicone	Standard	3/16"	7/8"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-13	Strip	Closed Cell	Silicone	Standard	3/16"	1"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3
ZUSA731AMFS-19	Strip	Closed Cell	Silicone	Standard	3/16"	1 1/2"	10 ft.	Red	Medium (9 - 13 psi)	High Temperature Adhesive	Textured	ASTM D1056 2D3