

High Temperature Silicone Foam

Cords are often used to fill gaps, channels, and make custom seals. Foam is easy to compress and conforms to uneven surfaces. Silicone is the go to choice for high temperature applications.



Part Number	Shape	Cell Type	Material	Grade	Cross Section	Length	Color	Firmness	Texture	Specs Met
ZUSASSR-C-1	Cord	Closed Cell	Silicone	Standard	1/8"	100 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-2	Cord	Closed Cell	Silicone	Standard	3/16"	100 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-3	Cord	Closed Cell	Silicone	Standard	1/4"	100 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-4	Cord	Closed Cell	Silicone	Standard	3/8"	100 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-5	Cord	Closed Cell	Silicone	Standard	1/2"	100 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-6	Cord	Closed Cell	Silicone	Standard	1/8"	10 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-7	Cord	Closed Cell	Silicone	Standard	3/16"	10 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-8	Cord	Closed Cell	Silicone	Standard	1/4"	10 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-9	Cord	Closed Cell	Silicone	Standard	3/8"	10 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3
ZUSASSR-C-10	Cord	Closed Cell	Silicone	Standard	1/2"	10 ft.	Red	Medium (9 - 13 psi)	Smooth	ASTM D1056 2D3

Oil Resistant Buna-N Foam

Cords are often used to fill gaps, channels, and make custom seals. Foam is easy to compress and conforms to uneven surfaces. Buna-N is commonly used because of its excellent oil resistance.



Part Number	Shape	Cell Type	Material	Grade	Cross Section	Length	Color	Firmness	Texture	Specs Met
ZUSABSR-C-1	Cord	Closed Cell	Buna-N	Standard	1/8"	25 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2B3
ZUSABSR-C-2	Cord	Closed Cell	Buna-N	Standard	0.139"	25 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2B3
ZUSABSR-C-5	Cord	Closed Cell	Buna-N	Standard	1/4"	10 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2B3
ZUSABSR-C-3	Cord	Closed Cell	Buna-N	Standard	1/2"	10 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2B3
ZUSABSR-C-4	Cord	Closed Cell	Buna-N	Standard	1"	10 ft.	Black	Medium (9 - 13 psi)	Smooth	ASTM D1056 2B3