

Weather Resistant EPDM Foam

Used for filling gaps, making circular seals, or fabricated into round parts such as spacers, washers, or stoppers. EPDM is the most weather resistant foam, with a wide range of chemical compatibility, steam resistance, and good temperature range.



Part Number	Shape	Cell Type	Material	Grade	Length	ID	OD	Thickness	Color	Firmness	Texture	Specs Met
ZUSAESR-T-1	Tube	Closed Cell	EPDM	Standard	10 ft.	1/4"	3/4"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-2	Tube	Closed Cell	EPDM	Standard	10 ft.	3/8"	7/8"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-5	Tube	Closed Cell	EPDM	Standard	10 ft.	5/8"	7/8"	5/32"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-3	Tube	Closed Cell	EPDM	Standard	10 ft.	1/2"	1"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-6	Tube	Closed Cell	EPDM	Standard	10 ft.	7/8"	1-5/16"	7/32"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-4	Tube	Closed Cell	EPDM	Standard	10 ft.	3/4"	1-1/4"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-7	Tube	Closed Cell	EPDM	Standard	10 ft.	1"	1-1/2"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-8	Tube	Closed Cell	EPDM	Standard	10 ft.	1-1/8"	1-3/4"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-9	Tube	Closed Cell	EPDM	Standard	10 ft.	1-1/4"	1-7/8"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-10	Tube	Closed Cell	EPDM	Standard	10 ft.	1-3/8"	2"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-13	Tube	Closed Cell	EPDM	Standard	5 ft.	1/4"	3/4"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-14	Tube	Closed Cell	EPDM	Standard	5 ft.	3/8"	7/8"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-15	Tube	Closed Cell	EPDM	Standard	5 ft.	5/8"	7/8"	5/32"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-16	Tube	Closed Cell	EPDM	Standard	5 ft.	1/2"	1"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-17	Tube	Closed Cell	EPDM	Standard	5 ft.	7/8"	1-5/16"	7/32"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-18	Tube	Closed Cell	EPDM	Standard	5 ft.	3/4"	1-1/4"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-19	Tube	Closed Cell	EPDM	Standard	5 ft.	1"	1-1/2"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-20	Tube	Closed Cell	EPDM	Standard	5 ft.	1-1/8"	1-3/4"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-21	Tube	Closed Cell	EPDM	Standard	5 ft.	1-1/4"	1-7/8"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-22	Tube	Closed Cell	EPDM	Standard	5 ft.	1-3/8"	2"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-25	Tube	Closed Cell	EPDM	Standard	2 ft.	1/4"	3/4"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-26	Tube	Closed Cell	EPDM	Standard	2 ft.	3/8"	7/8"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-27	Tube	Closed Cell	EPDM	Standard	2 ft.	5/8"	7/8"	5/32"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-28	Tube	Closed Cell	EPDM	Standard	2 ft.	1/2"	1"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-29	Tube	Closed Cell	EPDM	Standard	2 ft.	7/8"	1-5/16"	7/32"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-30	Tube	Closed Cell	EPDM	Standard	2 ft.	3/4"	1-1/4"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-31	Tube	Closed Cell	EPDM	Standard	2 ft.	1"	1-1/2"	1/4"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-32	Tube	Closed Cell	EPDM	Standard	2 ft.	1-1/8"	1-3/4"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-33	Tube	Closed Cell	EPDM	Standard	2 ft.	1-1/4"	1-7/8"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2
ZUSAESR-T-34	Tube	Closed Cell	EPDM	Standard	2 ft.	1-3/8"	2"	5/16"	Black	Soft (5 - 8 psi)	Smooth	ASTM D1056 2A2