

Textured Neoprene Rubber

These sheets have a crisscross texture that provides a nonslip gripping surface. Neoprene has a good balance of properties and is suitable for oils, water, and refrigerants.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-N40TXT-7	Sheet	Neoprene	Standard	40A	1/32"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-19	Sheet	Neoprene	Standard	40A	1/32"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-49	Sheet	Neoprene	Standard	40A	1/32"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-55	Sheet	Neoprene	Standard	40A	1/32"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-61	Sheet	Neoprene	Standard	40A	1/32"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-8	Sheet	Neoprene	Standard	40A	1/16"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-20	Sheet	Neoprene	Standard	40A	1/16"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-50	Sheet	Neoprene	Standard	40A	1/16"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-56	Sheet	Neoprene	Standard	40A	1/16"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-62	Sheet	Neoprene	Standard	40A	1/16"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-9	Sheet	Neoprene	Standard	40A	3/32"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-21	Sheet	Neoprene	Standard	40A	3/32"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-51	Sheet	Neoprene	Standard	40A	3/32"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-57	Sheet	Neoprene	Standard	40A	3/32"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-63	Sheet	Neoprene	Standard	40A	3/32"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-10	Sheet	Neoprene	Standard	40A	1/8"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-22	Sheet	Neoprene	Standard	40A	1/8"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-52	Sheet	Neoprene	Standard	40A	1/8"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-58	Sheet	Neoprene	Standard	40A	1/8"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-64	Sheet	Neoprene	Standard	40A	1/8"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-11	Sheet	Neoprene	Standard	40A	3/16"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-23	Sheet	Neoprene	Standard	40A	3/16"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-53	Sheet	Neoprene	Standard	40A	3/16"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-59	Sheet	Neoprene	Standard	40A	3/16"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-65	Sheet	Neoprene	Standard	40A	3/16"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-12	Sheet	Neoprene	Standard	40A	1/4"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-24	Sheet	Neoprene	Standard	40A	1/4"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-54	Sheet	Neoprene	Standard	40A	1/4"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-60	Sheet	Neoprene	Standard	40A	1/4"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N40TXT-66	Sheet	Neoprene	Standard	40A	1/4"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 407
BULK-RS-N50TXT-7	Sheet	Neoprene	Standard	50A	1/32"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-19	Sheet	Neoprene	Standard	50A	1/32"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-49	Sheet	Neoprene	Standard	50A	1/32"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-55	Sheet	Neoprene	Standard	50A	1/32"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-61	Sheet	Neoprene	Standard	50A	1/32"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-8	Sheet	Neoprene	Standard	50A	1/16"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-20	Sheet	Neoprene	Standard	50A	1/16"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-50	Sheet	Neoprene	Standard	50A	1/16"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-56	Sheet	Neoprene	Standard	50A	1/16"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-62	Sheet	Neoprene	Standard	50A	1/16"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-9	Sheet	Neoprene	Standard	50A	3/32"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-21	Sheet	Neoprene	Standard	50A	3/32"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-51	Sheet	Neoprene	Standard	50A	3/32"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-57	Sheet	Neoprene	Standard	50A	3/32"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-63	Sheet	Neoprene	Standard	50A	3/32"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-10	Sheet	Neoprene	Standard	50A	1/8"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-22	Sheet	Neoprene	Standard	50A	1/8"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-52	Sheet	Neoprene	Standard	50A	1/8"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-58	Sheet	Neoprene	Standard	50A	1/8"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-64	Sheet	Neoprene	Standard	50A	1/8"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-11	Sheet	Neoprene	Standard	50A	3/16"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-23	Sheet	Neoprene	Standard	50A	3/16"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-53	Sheet	Neoprene	Standard	50A	3/16"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-59	Sheet	Neoprene	Standard	50A	3/16"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-65	Sheet	Neoprene	Standard	50A	3/16"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-12	Sheet	Neoprene	Standard	50A	1/4"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-24	Sheet	Neoprene	Standard	50A	1/4"	12"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-54	Sheet	Neoprene	Standard	50A	1/4"	36"	12"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-60	Sheet	Neoprene	Standard	50A	1/4"	36"	24"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N50TXT-66	Sheet	Neoprene	Standard	50A	1/4"	36"	36"	Black	Plain	Textured	ASTM D2000 BC 507
BULK-RS-N60TXT-7	Sheet	Neoprene	Standard	60A	1/32"	12"	12"	Black	Plain	Textured	ASTM D2000 BC 607