

Metal Detectable FDA Buna-N Rubber

This formulation contains metal fillers which allow the Buna-N rubber to be picked up by metal detection systems should they tear or fall into the process stream. It is also made of FDA compliant materials for food, beverage, and pharmaceutical applications. Buna-N is ideal for oils, grease, fuels, and petroleum applications. It also works well with water and mild chemicals and has excellent physical properties making it tough and durable.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-H60MD-1	Roll	Buna-N	Metal Detectable	60A	1/32"	36"	60 ft.	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-2	Roll	Buna-N	Metal Detectable	60A	1/16"	36"	60 ft.	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-3	Roll	Buna-N	Metal Detectable	60A	1/8"	36"	60 ft.	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-4	Roll	Buna-N	Metal Detectable	60A	3/16"	36"	50 ft.	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-5	Roll	Buna-N	Metal Detectable	60A	1/4"	36"	50 ft.	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-6	Sheet	Buna-N	Metal Detectable	60A	1/32"	6"	6"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-7	Sheet	Buna-N	Metal Detectable	60A	1/16"	6"	6"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-8	Sheet	Buna-N	Metal Detectable	60A	1/8"	6"	6"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-9	Sheet	Buna-N	Metal Detectable	60A	3/16"	6"	6"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-10	Sheet	Buna-N	Metal Detectable	60A	1/4"	6"	6"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-11	Sheet	Buna-N	Metal Detectable	60A	1/32"	12"	12"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-12	Sheet	Buna-N	Metal Detectable	60A	1/16"	12"	12"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-13	Sheet	Buna-N	Metal Detectable	60A	1/8"	12"	12"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-14	Sheet	Buna-N	Metal Detectable	60A	3/16"	12"	12"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-15	Sheet	Buna-N	Metal Detectable	60A	1/4"	12"	12"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-16	Sheet	Buna-N	Metal Detectable	60A	1/32"	24"	24"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-17	Sheet	Buna-N	Metal Detectable	60A	1/16"	24"	24"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-18	Sheet	Buna-N	Metal Detectable	60A	1/8"	24"	24"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-19	Sheet	Buna-N	Metal Detectable	60A	3/16"	24"	24"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-20	Sheet	Buna-N	Metal Detectable	60A	1/4"	24"	24"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-21	Sheet	Buna-N	Metal Detectable	60A	1/32"	36"	36"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-22	Sheet	Buna-N	Metal Detectable	60A	1/16"	36"	36"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-23	Sheet	Buna-N	Metal Detectable	60A	1/8"	36"	36"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-24	Sheet	Buna-N	Metal Detectable	60A	3/16"	36"	36"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-25	Sheet	Buna-N	Metal Detectable	60A	1/4"	36"	36"	Blue	Plain	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-26	Sheet	Buna-N	Metal Detectable	60A	1/32"	6"	6"	Blue	Acrylic Adhesive	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-27	Sheet	Buna-N	Metal Detectable	60A	1/16"	6"	6"	Blue	Acrylic Adhesive	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-28	Sheet	Buna-N	Metal Detectable	60A	1/8"	6"	6"	Blue	Acrylic Adhesive	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-29	Sheet	Buna-N	Metal Detectable	60A	3/16"	6"	6"	Blue	Acrylic Adhesive	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-30	Sheet	Buna-N	Metal Detectable	60A	1/4"	6"	6"	Blue	Acrylic Adhesive	Smooth	ASTM D2000 BF 607
BULK-RS-H60MD-31	Sheet	Buna-N	Metal Detectable	60A	1/32"	12"	12"	Blue	Acrylic Adhesive	Smooth	ASTM D2000 BF 607