

Plastic Bands

Polypropylene pipe

Mounting brackets for polypropylene vertical bands and polypropylene spectacle bands

Polypropylene pipe (white)

Units (mm)

Part number	Size code	Applicable band size	Bracket pipe diameter	Bracket pipe length
A10499	0013	15A to 50A	16	1000
A10500	0016	65A to 100A	20	1000

Polypropylene pipe (gray)

Units (mm)

Part number	Size code	Applicable band size	Bracket pipe diameter	Bracket pipe length
A10501	0013	15A to 50A	16	1000
A10503	0018	65A to 100A	20	1000

Polypropylene pipe (ivory)


Units (mm)

Part number	Size code	Applicable band size	Bracket pipe diameter	Bracket pipe length
A10504	0015	15A to 50A	16	1000

Polypropylene pipe (beige)

Units (mm)

Part number	Size code	Applicable band size	Bracket pipe diameter	Bracket pipe length
A10505	0012	15A to 50A	16	1000
A10506	0010	65A to 100A	20	1000



Polypropylene vertical bracket

Mounting brackets for polypropylene vertical bands


Polypropylene vertical bracket (Small)

Applicable band

15A to 50A

Units (mm)

Code No.		A10468	A10470	A10472	A10473
Bracket dimension	Bracket pipe diameter	White	Gray	Ivory	Beige
50L	16	0017	0015	0010	0017
65L	16	0021	0020	0062	0021
75L	16	0036	0034	0024	0036
100L	16	0055	0049	0039	0055
125L	16	0060	0053	0077	0060
150L	16	0074	0068	0043	0074
200L	16	0089	0072	0058	0089




Polypropylene vertical bracket (Large)

Applicable band

65A to 100A

Units (mm)

Code No.		A10469	A10471	A10474
Bracket dimension	Bracket pipe diameter	White	Gray	Beige
65L	20	0029	0027	0029
75L	20	0033	0031	0033
100L	20	0048	0046	0048
125L	20	0052	0065	0052
150L	20	0067	0070	0067
200L	20	0071	0084	0071



Polypropylene vertical pedestal

Mounting pedestals for polypropylene vertical bands

Polypropylene vertical pedestal (Small)

Applicable band

15A to 50A

Units (mm)

Part number	Size code	Color
A10475	0011	White
A10477	0016	Gray
A10480	0011	Ivory
A10481	0019	Beige



Polypropylene vertical pedestal (Large)

Applicable band

65A to 100A

Units (mm)

Part number	Size code	Color
A10476	0019	White
A10478	0013	Gray
A10482	0016	Beige

