

**BCT-S9 / BCT-S9Z / BCT-S7 / BCT-S5**

**BOLT CATCH HOLDER SET (mm. size / inch size)**

SURFACE TREATMENT : EL/ARMOUR plated / PACKAGE : Slide blister pack



BCT-S9



BCT-S9Z



BCT-S7



BCT-S5

Item No.	Pcs.	H										Inner	D×W×H	g
BCT-S5	5	2.5	3	4	5	6						10	256×160×53	1,510
BCT-S7	7	2.5	3	4	5	6	8	10				5	311×120×68	2,330
BCT-S9	9	※1.5	※2	2.5	3	4	5	6	8	10		5	305×99×111	2,431
BCT-S9Z	9	※1/16	※5/64	3/32	1/8	5/32	3/16	1/4	5/16	3/8		5	305×99×111	2,334

※No Fit Ring on 1.5mm and 2 mm.

※No Fit Ring on 1/16 " and 5/64"

※The holder colour of BCT-S9Z is different from BCT-S9.


**BCT-\***

**BOLT CATCH INDIVIDUAL (mm. size / inch size)**

SURFACE TREATMENT : EL/ARMOUR plated / PACKAGE : Bulk pack



BCT-6



Item No.	H	L1	L2	Inner	D×W×H	g
BCT-2.5	2.5	18	110	20	162×68×35	140
BCT-3	3	20	126	20	162×68×35	205
BCT-4	4	25	142	20	162×68×35	390
BCT-5	5	28	160	20	202×65×32	660
BCT-6	6	32	180	20	226×75×32	1,060
BCT-8	8	36	200	10	226×75×32	1,047
BCT-10	10	40	224	10	250×90×38	1,820

※Pack packaging is also available.

Item No.	H	L1	L2	Inner	D×W×H	g
BCT-3/32	3/32"	18	108	20	162×68×35	128
BCT-1/8	1/8"	20	127	20	162×68×35	228
BCT-5/32	5/32"	25	140	20	162×68×35	368
BCT-3/16	3/16"	28	158	20	202×65×32	591
BCT-1/4	1/4"	32	178	20	226×75×32	1,157
BCT-5/16	5/16"	36	198	10	226×75×32	1,017
BCT-3/8	3/8"	40	222	10	250×90×38	1,630

※Pack packaging is also available.

EXCELLENT

STANDARD

TORX®

IOB&Co.

L  
TYPE

KNIFE  
TYPE

SCREW DRIVER  
TYPE

T-HANDLE  
TYPE

SOCKET BIT  
TYPE

BIT  
TYPE



Please be sure to read "Attention on use" in the appendix.