



44.9	38.3	5	41.1	38.7	35	29-11-0152	5240-15	15
37.4	30.8	5	33.6	31.2	27.5	-0122	-12	12
34.9	28.3	5	31.1	28.7	25	-0112	-11	11
32.4	25.8	5	28.6	26.2	22.5	-0102	-10	10
29.9	23.3	5	26.1	23.7	20	-0092	-09	9
27.4	20.8	5	23.6	21.2	17.5	-0082	-08	8
24.9	18.3	5	21.1	18.7	15	-0072	-07	7
22.4	15.8	5	18.6	16.2	12.5	-0062	-06	6
19.9	13.3	3.75	16.1	13.7	10	-0052	-05	5
17.4	10.8	7.5	13.6	11.2	7.5	-0042	-04	4
14.9	8.3	5	11.1	8.7	5	-0032	-03	3
12.4	5.8	2.5	8.6	6.2	2.5	29-11-0022	5240-02	2
F	(E)	(D)	(C)	B	A	EDP. NO.	MATERIAL NO.	極致 NO. OF CKT.

注記 NOTE

△ 4極までは1箇所、5極以上は2箇所。
 FRICTION LOCK CONFIGURATION:
 4CKT. AND UNDER 1 LOCK
 5CKT. AND OVER 2 LOCKS

2. 嵌合相手: 5102-N
 MATE WITH HOUSING: 5102-N

△ 4極以下はなし、5及び6極は1箇所、7極以上は2箇所。
 SLIT CONFIGURATION:
 4CKT. AND UNDER NO SLIT
 5 AND 6CKTS 1 SLIT
 7CKT. AND OVER 2 SLIT

材料 MATERIAL
 NYLON66,UL94V-0

REVISED JEC NO: J2009-0885 T. DRINKAKUMURA 2008/12/15 CHIKOJI HARUYAMA 2008/12/15 APPR: NUKITA 2009/01/14	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY	SCALE ---	DESIGN UNITS METRIC	MODEL NO. 5240-N
	10 UNDER	±0.2	DRAWN BY Y. KANNO	DATE '98/7/23	TITLE MINI SPOX. PLUG HSG.	THIRD ANGLE PROJECTION
	10 OVER 30 UNDER	±0.25	CHECKED BY K. T	DATE '98/7/24		
	30 OVER	±0.30	APPROVED BY M. FUKUSHIMA	DATE '98/7/24		
	ANGULAR	±3 °	MATERIAL NO.	DOCUMENT NO.	MOLEX INCORPORATED	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	SEE TABLE	SD-5240-001	SHEET NO. 1 OF 1