


Ball-Point Hexagonal Wrenches (inch size)

The number next to the logo mark indicates items in stock for each brand.


Stock
38,650
Items

Ball-Point Hexagonal Wrench (inch size)



- Features**
- Can be used by tilting about 25° by Ball-point machining, temporary fastening of bolts quickly, usability improves.
 - I am performing a black dye process.
- Materials**
- Chrome Vanadium Steel (Cr-V)
- Origin**
- Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (inch)	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
445-5274	TBRI-0.05	¥130	¥140	0.05	12	72	50	0.97
445-5282	TBRI-1/16	¥148	¥160	1/16	14	77	50	1.60
445-5371	TBRI-5/64	¥148	¥160	5/64	15	82	50	2.60
445-5339	TBRI-3/32	¥148	¥160	3/32	17	88	50	4.10
445-5398	TBRI-7/64	¥158	¥170	7/64	18	92	50	5.89
445-5312	TBRI-1/8	¥158	¥170	1/8	19	96	50	8.00
445-5401	TBRI-9/64	¥185	¥200	9/64	20	101	50	10.60
445-5363	TBRI-5/32	¥185	¥200	5/32	21	105	50	13.70
445-5321	TBRI-3/16	¥194	¥210	3/16	24	114	50	21.60
445-5380	TBRI-7/32	¥222	¥240	7/32	26	124	50	31.90
445-5304	TBRI-1/4	¥249	¥270	1/4	28	135	40	45.50
445-5355	TBRI-5/16	¥324	¥350	5/16	32	151	30	79.80
445-5347	TBRI-3/8	¥417	¥450	3/8	35	170	20	128.60

Set Features • Since the holder rotates, it is easy to put in and out each size of hexagonal wrench.

Order Unit: 1 Set


Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (inch)	Set Contents (piece)	SPQ (set)	Weight (g/set)
445-5410	TBRI-9S	¥2,314	¥2,500	5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	9	6	351
445-5291	TBRI-13S	¥2,962	¥3,200	0.05, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	13	6	390

Contact us: 0120-509-849 <http://www.orange-book.com/>

EIGHT


Stock
252
Items

Hexagonal Key Spanner Ball-Point (semi-long/inch size)



- Features**
- Can be used by tilting about 25° since the ball point is machined into a spherical shape, temporary fastening of bolts quickly, usability improves.

Materials

- Wrench: Special Alloy Steel, SNCM+V (black dye parkerizing)

Origin

- Japan

Order Unit: 1 Piece

EIGHT TOOL Co.Ltd.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (inch)	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
401-2143	016-0.05INCH	¥255	¥330	0.05	14	75	10	1.0
401-2178	016-1/16INCH	¥293	¥380	1/16	15	79	10	1.5
401-2321	016-5/64INCH	¥293	¥380	5/64	17	84	10	2.5
401-2267	016-3/32INCH	¥293	¥380	3/32	17	92	10	4.0
401-2364	016-7/64INCH	¥309	¥400	7/64	19	97	10	6.0
401-2224	016-1/8INCH	¥309	¥400	1/8	20	102	10	8.0
401-2381	016-9/64INCH	¥370	¥480	9/64	23	104	10	11.0
401-2313	016-5/32INCH	¥370	¥480	5/32	25	108	10	14.0
401-2259	016-3/16INCH	¥393	¥510	3/16	28	118	10	22.0
401-2356	016-7/32INCH	¥447	¥580	7/32	30	125	10	32.0
401-2194	016-1/4INCH	¥501	¥650	1/4	32	135	10	44.5
401-2305	016-5/16INCH	¥640	¥830	5/16	36	152	10	79.0
401-2275	016-3/8INCH	¥818	¥1,060	3/8	40	170	10	127.5

Set Accessories • Holder

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (inch)	Set Contents (piece)	SPQ (set)	Weight (g/set)
401-2186	016-13ZD	¥4,644	¥6,020	0.05, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 5/16, 3/8	13	5	426

Contact us: 06-6793-9025 <http://www.eight-tool.co.jp/>

EIGHT


Stock
252
Items

Hexagonal Key Spanner Set (extra long/inch size)



- Features**
- The tapered head, has improved durability and abrasion resistance so that it can be used for final tightening. 10 to 20% torsional strength is higher than conventional ball end, and it is particularly effective for use with inclination (0 to 20°).
 - The door holder has no resistance against the wrench and can be taken in and out easily. Just close the door after use and the wrench will be aligned to the original position.

Accessories

- Holder

Origin

- Japan

Order Unit: 1 Set

EIGHT TOOL Co.Ltd.

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (inch)	Set Contents (piece)	SPQ (set)	Weight (g/set)
360-5485	TEL-S9ZD	¥8,385	¥10,870	1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 1/4, 5/16, 3/8	9	5	430

Contact us: 06-6793-9025 <http://www.eight-tool.co.jp/>