



Stock
38,650
Items

Hex Lobe Wrench



Features •Corresponds to hexalobular screw with the anti-tampering screw. •The surface treatment is electroless nickel plating.
Materials •Chrome Vanadium Steel Origin •Japan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Blade Edge	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
336-1845	THX-10	¥593	¥640	T10H	18	56	10	3.5
336-1853	THX-15	¥638	¥690	T15H	20	63	10	8.0
336-1861	THX-20	¥676	¥730	T20H	23	72	10	8.5
336-1870	THX-25	¥750	¥810	T25H	28	80	10	14.0
336-1888	THX-27	¥759	¥820	T27H	32	90	10	25.0
336-1896	THX-30	¥796	¥860	T30H	36	100	10	28.0
336-1900	THX-40	¥852	¥920	T40H	40	112	10	44.0

Set Accessories •Holder


Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Set Contents (piece)	SPQ (set)	Weight (g/set)
336-1918	THX-7S	¥4,897	¥5,290	T10H, T15H, T20H, T25H, T27H, T30H, T40H	7	10	170

Contact us:0120-509-849 <http://www.orange-book.com/>

Stock
38,650
Items

Hex Lobe Wrench



Features •Compared with popular products, high torque, durability and wear resistance are outstandingly excellent.
•Corresponds to hexalobular screw with the anti-tampering screw.
•Matte chrome plating.
Materials •Chrome Vanadium Steel
Origin •Taiwan



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Blade Edge	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
445-3565	TTW-8H	¥379	¥410	T8H	16	80	50	6.7
445-3573	TTW-10H	¥407	¥440	T10H	17	86	50	7.2
445-3581	TTW-15H	¥426	¥460	T15H	18	90	50	7.5
445-3590	TTW-20H	¥435	¥470	T20H	19	95	50	12.0
445-3603	TTW-25H	¥463	¥500	T25H	20	100	50	19.0
445-3611	TTW-27H	¥482	¥520	T27H	22	105	50	20.0
445-3620	TTW-30H	¥509	¥550	T30H	24	114	50	29.0
445-3638	TTW-40H	¥555	¥600	T40H	26	124	40	42.0
445-3646	TTW-50H	¥787	¥850	T50H	32	152	20	80.0

Set Accessories •Holder


Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Set Contents (piece)	SPQ (set)	Weight (g/set)
301-1364	TTW-9S	¥4,582	¥4,950	T8H, T10H, T15H, T20H, T25H, T27H, T30H, T40H, T50H	9	6	250

Contact us:0120-509-849 <http://www.orange-book.com/>

Stock
38,650
Items

Hex Lobe Wrench



Features •The holder rotates, making it easy to put in and out wrenches of various sizes.
Materials •Nickel Chrome Molybdenum Steel
Origin •Taiwan

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Blade Edge	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
389-6668	THR-6H	¥231	¥250	T6H	16	75	50	6.30
389-6676	THR-7H	¥241	¥260	T7H	16	80	50	6.65
389-6684	THR-8H	¥241	¥260	T8H	16	80	50	6.65
389-6692	THR-9H	¥259	¥280	T9H	16	83	50	6.85
389-6706	THR-10H	¥269	¥290	T10H	17	86	50	7.12
389-6714	THR-15H	¥278	¥300	T15H	18	90	50	7.47
389-6722	THR-20H	¥287	¥310	T20H	19	95	50	12.30
389-6731	THR-25H	¥296	¥320	T25H	20	100	50	18.70
389-6749	THR-27H	¥306	¥330	T27H	22	105	50	19.83
389-6757	THR-30H	¥324	¥350	T30H	24	114	50	29.31
389-6765	THR-40H	¥361	¥390	T40H	26	124	40	41.37
389-6773	THR-45H	¥472	¥510	T45H	29	133	30	70.73
389-6781	THR-50H	¥509	¥550	T50H	32	152	20	80.18

Set Accessories •Holder

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents	Set Contents (piece)	SPQ (set)	Weight (g/set)
389-6790	THR-9S	¥2,953	¥3,190	T8H, T10H, T15H, T20H, T25H, T27H, T30H, T40H, T50H	9	6	250
389-6803	THR-12S	¥3,666	¥3,960	T7H, T8H, T9H, T10H, T15H, T20H, T25H, T27H, T30H, T40H, T45H, T50H	12	6	366

Contact us:0120-509-849 <http://www.orange-book.com/>