


Multipurpose Neoprene Foam

Neoprene Foam

Neoprene is the most commonly used foam material due to its good balance of strength, oil, water, and weather resistance. Common applications include industrial gaskets to seal water, air, dust, and other environmental items, automotive gaskets, and athletic equipment.



| Part Number | Shape | Cell Type | Material | Grade | Thickness | Width | Length | Color | Firmness | Backing Type | Texture | Specs Met |
|-------------|-------|-------------|----------|----------|-----------|-------|--------|-------|---------------------|------------------|---------|---------------------------|
| ZUSANSR-101 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 1/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-108 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-113 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 3/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-118 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 1" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-102 | Strip | Closed Cell | Neoprene | Standard | 1/8" | 1/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-109 | Strip | Closed Cell | Neoprene | Standard | 1/8" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-114 | Strip | Closed Cell | Neoprene | Standard | 1/8" | 3/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-119 | Strip | Closed Cell | Neoprene | Standard | 1/8" | 1" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-103 | Strip | Closed Cell | Neoprene | Standard | 1/4" | 1/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-110 | Strip | Closed Cell | Neoprene | Standard | 1/4" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-115 | Strip | Closed Cell | Neoprene | Standard | 1/4" | 3/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-120 | Strip | Closed Cell | Neoprene | Standard | 1/4" | 1" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-111 | Strip | Closed Cell | Neoprene | Standard | 3/8" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-116 | Strip | Closed Cell | Neoprene | Standard | 3/8" | 3/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-121 | Strip | Closed Cell | Neoprene | Standard | 3/8" | 1" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-123 | Strip | Closed Cell | Neoprene | Standard | 3/8" | 2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-112 | Strip | Closed Cell | Neoprene | Standard | 1/2" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-117 | Strip | Closed Cell | Neoprene | Standard | 1/2" | 3/4" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-122 | Strip | Closed Cell | Neoprene | Standard | 1/2" | 1" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-124 | Strip | Closed Cell | Neoprene | Standard | 1/2" | 2" | 10 ft. | Black | Medium (9 - 13 psi) | Plain | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-192 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 1/8" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-196 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 3/16" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-186 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 1/4" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-187 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-188 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 5/8" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-189 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 3/4" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-190 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 1" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-191 | Strip | Closed Cell | Neoprene | Standard | 1/32" | 2" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-193 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 1/8" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-197 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 3/16" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-40 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 1/4" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-203 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 5/16" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |
| ZUSANSR-45 | Strip | Closed Cell | Neoprene | Standard | 1/16" | 1/2" | 10 ft. | Black | Medium (9 - 13 psi) | Acrylic Adhesive | Smooth | ASTM D1056 2C3, FMVSS-302 |