


Super Cushioning EVA Foam

EVA Foam

EVA foam resists tearing better than other types of foam and is used for shock absorption and cushioning. EVA is often fabricated into straps and padding.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture
ZUSA-EVA-31	Strip	Closed Cell	EVA	Standard	1/8"	1"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-32	Strip	Closed Cell	EVA	Standard	1/4"	1"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-33	Strip	Closed Cell	EVA	Standard	3/8"	1"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-34	Strip	Closed Cell	EVA	Standard	1/2"	1"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-35	Strip	Closed Cell	EVA	Standard	3/4"	1"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-36	Strip	Closed Cell	EVA	Standard	1"	1"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-1	Sheet	Closed Cell	EVA	Standard	1/8"	12"	12"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-7	Sheet	Closed Cell	EVA	Standard	1/8"	36"	36"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-2	Sheet	Closed Cell	EVA	Standard	1/4"	12"	12"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-8	Sheet	Closed Cell	EVA	Standard	1/4"	36"	36"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-3	Sheet	Closed Cell	EVA	Standard	3/8"	12"	12"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-9	Sheet	Closed Cell	EVA	Standard	3/8"	36"	36"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-4	Sheet	Closed Cell	EVA	Standard	1/2"	12"	12"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-10	Sheet	Closed Cell	EVA	Standard	1/2"	36"	36"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-5	Sheet	Closed Cell	EVA	Standard	3/4"	12"	12"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-11	Sheet	Closed Cell	EVA	Standard	3/4"	36"	36"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-6	Sheet	Closed Cell	EVA	Standard	1"	12"	12"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-12	Sheet	Closed Cell	EVA	Standard	1"	36"	36"	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-13	Sheet	Closed Cell	EVA	Standard	1/8"	12"	12"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-19	Sheet	Closed Cell	EVA	Standard	1/8"	36"	36"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-14	Sheet	Closed Cell	EVA	Standard	1/4"	12"	12"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-20	Sheet	Closed Cell	EVA	Standard	1/4"	36"	36"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-15	Sheet	Closed Cell	EVA	Standard	3/8"	12"	12"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-21	Sheet	Closed Cell	EVA	Standard	3/8"	36"	36"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-16	Sheet	Closed Cell	EVA	Standard	1/2"	12"	12"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-22	Sheet	Closed Cell	EVA	Standard	1/2"	36"	36"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-17	Sheet	Closed Cell	EVA	Standard	3/4"	12"	12"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-23	Sheet	Closed Cell	EVA	Standard	3/4"	36"	36"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-18	Sheet	Closed Cell	EVA	Standard	1"	12"	12"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-24	Sheet	Closed Cell	EVA	Standard	1"	36"	36"	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-25	Roll	Closed Cell	EVA	Standard	1/8"	36"	9 ft.	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-26	Roll	Closed Cell	EVA	Standard	1/4"	36"	9 ft.	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-27	Roll	Closed Cell	EVA	Standard	3/8"	36"	9 ft.	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-28	Roll	Closed Cell	EVA	Standard	1/2"	36"	9 ft.	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-29	Roll	Closed Cell	EVA	Standard	3/4"	36"	9 ft.	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-30	Roll	Closed Cell	EVA	Standard	1"	36"	9 ft.	Black	Firm (14+ psi)	Plain	Smooth
ZUSA-EVA-43	Roll	Closed Cell	EVA	Standard	1/8"	36"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-44	Roll	Closed Cell	EVA	Standard	1/4"	36"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-45	Roll	Closed Cell	EVA	Standard	3/8"	36"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-46	Roll	Closed Cell	EVA	Standard	1/2"	36"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-47	Roll	Closed Cell	EVA	Standard	3/4"	36"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth
ZUSA-EVA-48	Roll	Closed Cell	EVA	Standard	1"	36"	9 ft.	Black	Firm (14+ psi)	Acrylic Adhesive	Smooth