



ファスナー

ラッチ錠

ドア  
キャッチ

スナッチ  
ロック

コントロール  
センター

太陽光  
関連金具

グレーチング  
ロック

工業用  
錠前

電磁波  
対策

パッキン

窓枠・カード  
ホルダー

ゴム脚・  
グロメット

周辺機器  
(C)

充電器用  
金具

フリーザー  
金具

ラッシング  
システム


C-1533・C-533 小型ファスナー

# 扉止めファスナー FASTENERS



**C-1533**  
ステンレス製

**C-533**  
亜鉛合金・黄銅製



C-533-1

C-533-5

C-533-9-N

C-533-10-N

## 特徴 Feature

- ステンレス製で耐食性に優れています。(C-1533)
- 締付け型で扉・蓋をしっかり固定します。
- Corrosion-resistant stainless steel is used. (C-1533)
- Tightening type. To positively secure doors and covers.


## 仕様

- 〔C-1533〕 ● 材質：ステンレス鋼铸件(SUS304)  
● 表面仕上：バレル研磨
- 〔C-533-□N〕 ● 材質：亜鉛合金(ZDC)  
● 表面仕上：サチライトクロムめっき(MZCr)
- 〔C-533〕 ● 材質：快削黄銅棒(C3602BD)  
● 表面仕上：ニッケルめっき(MBNI)
- 用途 ● 計測機器・小型分電盤・点検口
- 納期 ● 標準在庫品
- 備考 ● C-533-1以外の品番の取付けは、ツマミ部分のイモねじを外し、ツマミを外して行って下さい。  
● 1.5mm用六角レンチをご使用下さい。


## Specifications

- 〔C-1533〕 ● Material: Cast stainless steel (SUS304)  
● Finish: Barrel polishing
- 〔C-533-□N〕 ● Material: Zinc alloy (ZDC)  
● Finish: Satellite chrome plating (MZCr)
- 〔C-533〕 ● Material: Free cutting brass (C3602BD)  
● Finish: Nickel plating (MBNi)
- Specific ● Measuring equipment, small distribution use boards and inspection entrance.
- Remarks ● Use a 1.5mm hexagonal wrench

〔C-533-1〕




パネル穴明け寸法  
Panel drilling dimensions




※つまみを回すと止め金が約90°回転し、さらに回すと止め金が扉を締付けます。  
※When the knob is turned the catch rotates through approximately 90°; when the knob is turned further the catch fastens the door.

〔C-533-5〕




パネル穴明け寸法  
Panel drilling dimensions




※つまみを回すと止め金が約90°回転し、さらに回すと止め金が扉を締付けます。  
※When the knob is turned the catch rotates through approximately 90°; when the knob is turned further the catch fastens the door.

〔C-1533-9〕  
〔C-533-9-N〕




パネル穴明け寸法  
Panel drilling dimensions




※つまみを回すと止め金が約90°回転し、さらに回すと止め金が扉を締付けます。  
※When the knob is turned the catch rotates through approximately 90°; when the knob is turned further the catch fastens the door.

〔C-1533-10〕  
〔C-533-10-N〕



パネル穴明け寸法  
Panel drilling dimensions



※つまみを押しながら約90°回転させます。スプリングの作用で扉を締付けます。  
※Push the knob and turn it through approximately 90°. Spring action will close the door.

## 特注ファスナー Custom-made fasteners



C-533-6



C-533-8

特注品・詳細寸法・納期はお問合せ下さい。

商品番号 Product No.	RoHS	CAD	材質 Material	製品質量(g) Mass	コード Code	単価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
C-1533-9	●	2D	SUS		22330	¥900	10個~	¥855
C-1533-10	●	2D	SUS		22331	¥1,100	10個~	¥1,045
C-533-1	●	2D/3D	黄銅 Brass	26	20751	¥440	20個~	¥422
C-533-5	●	2D/3D	黄銅 Brass	38	20754	¥630	20個~	¥605
C-533-9-N	●	2D	ZDC	26	22328	¥620	20個~	¥595
C-533-10-N	●	2D	ZDC	29	22329	¥720	20個~	¥691

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。 ※大量のご注文は更にお安くなります。