

Rings

High Temperature Silicone Foam

Used for filling gaps, making circular seals, or fabricated into round parts such as spacers, washers, or stoppers. Silicone is the go to choice for high temperature applications.



Part Number	Shape	Cell Type	Material	Grade	ID	OD	Thickness	Color	Firmness	Texture	Specs Met
ZUSASSR-R-1	Ring	Closed Cell	Silicone	Standard	1/2"	3/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-2	Ring	Closed Cell	Silicone	Standard	27/32"	1-1/8"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-3	Ring	Closed Cell	Silicone	Standard	1"	1-1/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-4	Ring	Closed Cell	Silicone	Standard	1"	1-1/2"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-5	Ring	Closed Cell	Silicone	Standard	1-1/16"	2-1/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-6	Ring	Closed Cell	Silicone	Standard	1-5/16"	2-5/8"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-7	Ring	Closed Cell	Silicone	Standard	1-1/2"	1-3/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-8	Ring	Closed Cell	Silicone	Standard	1-1/2"	2"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-9	Ring	Closed Cell	Silicone	Standard	2"	2-1/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-10	Ring	Closed Cell	Silicone	Standard	2"	2-1/2"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-11	Ring	Closed Cell	Silicone	Standard	2-3/8"	4-1/8"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-12	Ring	Closed Cell	Silicone	Standard	2-1/2"	2-3/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-13	Ring	Closed Cell	Silicone	Standard	2-1/2"	3"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-14	Ring	Closed Cell	Silicone	Standard	3"	3-1/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-15	Ring	Closed Cell	Silicone	Standard	3"	3-1/2"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-16	Ring	Closed Cell	Silicone	Standard	3-1/2"	3-3/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-17	Ring	Closed Cell	Silicone	Standard	3-1/2"	4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-18	Ring	Closed Cell	Silicone	Standard	3-1/2"	5-3/8"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-19	Ring	Closed Cell	Silicone	Standard	4"	4-1/4"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-20	Ring	Closed Cell	Silicone	Standard	4"	4-1/2"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3
ZUSASSR-R-21	Ring	Closed Cell	Silicone	Standard	4-1/2"	6-7/8"	1/8"	Red	Medium (9 - 13 psi)	Textured	ASTM D1056 2D3