


Ultra Strength Neoprene Rubber

This formulation is stronger and more durable than both Standard and High Strength Neoprene for the most demanding applications. Neoprene has a good balance of properties and is suitable for oils, water, and refrigerants while remaining tough and weather resistant.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-NUS50-268	Strip	Neoprene	Ultra Strength	50A	1/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-282	Strip	Neoprene	Ultra Strength	50A	1/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-296	Strip	Neoprene	Ultra Strength	50A	1/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-269	Strip	Neoprene	Ultra Strength	50A	1/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-283	Strip	Neoprene	Ultra Strength	50A	1/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-297	Strip	Neoprene	Ultra Strength	50A	1/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-271	Strip	Neoprene	Ultra Strength	50A	1/4"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-285	Strip	Neoprene	Ultra Strength	50A	1/4"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-299	Strip	Neoprene	Ultra Strength	50A	1/4"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-272	Strip	Neoprene	Ultra Strength	50A	3/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-286	Strip	Neoprene	Ultra Strength	50A	3/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-300	Strip	Neoprene	Ultra Strength	50A	3/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-273	Strip	Neoprene	Ultra Strength	50A	1/2"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-287	Strip	Neoprene	Ultra Strength	50A	1/2"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS50-301	Strip	Neoprene	Ultra Strength	50A	1/2"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 517
BULK-RS-NUS60-57	Strip	Neoprene	Ultra Strength	60A	1/16"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-58	Strip	Neoprene	Ultra Strength	60A	1/16"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-59	Strip	Neoprene	Ultra Strength	60A	1/16"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-60	Strip	Neoprene	Ultra Strength	60A	1/16"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-268	Strip	Neoprene	Ultra Strength	60A	1/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-64	Strip	Neoprene	Ultra Strength	60A	1/16"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-282	Strip	Neoprene	Ultra Strength	60A	1/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-296	Strip	Neoprene	Ultra Strength	60A	1/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-97	Strip	Neoprene	Ultra Strength	60A	1/8"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-98	Strip	Neoprene	Ultra Strength	60A	1/8"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-99	Strip	Neoprene	Ultra Strength	60A	1/8"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-100	Strip	Neoprene	Ultra Strength	60A	1/8"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-269	Strip	Neoprene	Ultra Strength	60A	1/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-104	Strip	Neoprene	Ultra Strength	60A	1/8"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-283	Strip	Neoprene	Ultra Strength	60A	1/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-297	Strip	Neoprene	Ultra Strength	60A	1/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-87	Strip	Neoprene	Ultra Strength	60A	1/4"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-88	Strip	Neoprene	Ultra Strength	60A	1/4"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-89	Strip	Neoprene	Ultra Strength	60A	1/4"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-90	Strip	Neoprene	Ultra Strength	60A	1/4"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-271	Strip	Neoprene	Ultra Strength	60A	1/4"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-94	Strip	Neoprene	Ultra Strength	60A	1/4"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-285	Strip	Neoprene	Ultra Strength	60A	1/4"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-299	Strip	Neoprene	Ultra Strength	60A	1/4"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-272	Strip	Neoprene	Ultra Strength	60A	3/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-286	Strip	Neoprene	Ultra Strength	60A	3/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-300	Strip	Neoprene	Ultra Strength	60A	3/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-273	Strip	Neoprene	Ultra Strength	60A	1/2"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-287	Strip	Neoprene	Ultra Strength	60A	1/2"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS60-301	Strip	Neoprene	Ultra Strength	60A	1/2"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 617
BULK-RS-NUS70-268	Strip	Neoprene	Ultra Strength	70A	1/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-282	Strip	Neoprene	Ultra Strength	70A	1/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-296	Strip	Neoprene	Ultra Strength	70A	1/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-269	Strip	Neoprene	Ultra Strength	70A	1/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-283	Strip	Neoprene	Ultra Strength	70A	1/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-297	Strip	Neoprene	Ultra Strength	70A	1/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-271	Strip	Neoprene	Ultra Strength	70A	1/4"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-285	Strip	Neoprene	Ultra Strength	70A	1/4"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-299	Strip	Neoprene	Ultra Strength	70A	1/4"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-272	Strip	Neoprene	Ultra Strength	70A	3/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-286	Strip	Neoprene	Ultra Strength	70A	3/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-300	Strip	Neoprene	Ultra Strength	70A	3/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717
BULK-RS-NUS70-273	Strip	Neoprene	Ultra Strength	70A	1/2"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 717