


Fabric-Reinforced Neoprene Rubber

These sheets have a fabric insert and stand up to high stress and flex. They are often used as flange gaskets, diaphragm packing, and in other applications with heavy compression. Neoprene has a good balance of properties and is suitable for oils, water, and refrigerants.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-NFR60-5	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-9	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	12"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR70-312	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	24"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR60-21	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	48"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-25	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	48"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-29	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	48"	36"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-6	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-10	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	12"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR70-313	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	24"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR60-22	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	48"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-26	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	48"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-30	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	48"	36"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-7	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR70-310	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR60-11	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	12"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR70-314	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	24"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-318	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	36"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-306	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR60-23	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	48"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-27	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	48"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-31	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	48"	36"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-8	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-12	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	12"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR70-315	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	24"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR60-24	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	48"	12"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-28	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	48"	24"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-32	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	48"	36"	Black	Plain	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-61	Sheet	Neoprene	Fabric-Reinforced	60A	1/16"	48"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-62	Sheet	Neoprene	Fabric-Reinforced	60A	1/8"	48"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-63	Sheet	Neoprene	Fabric-Reinforced	60A	3/16"	48"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 607
BULK-RS-NFR60-64	Sheet	Neoprene	Fabric-Reinforced	60A	1/4"	48"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 607
BULK-RS-NNFR70-5	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 707
BULK-RS-NNFR70-9	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	12"	24"	Black	Plain	Smooth	ASTM D2000 BC 707