


Fabric-Reinforced High Strength Neoprene Rubber

These sheets have a fabric insert and stand up to high stress and flex. They are often used as flange gaskets, diaphragm packing, and in other applications with heavy compression. Neoprene has a good balance of properties and is suitable for oils, water, and refrigerants.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-NFR70-219	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	6"	6"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-23	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-9	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	36"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-235	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	36"	24"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-16	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	36"	36"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-220	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	6"	6"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-24	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-10	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	36"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-236	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	36"	24"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-17	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	36"	36"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-222	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	6"	6"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-26	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	12"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-12	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	36"	12"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-237	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	36"	24"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-19	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	36"	36"	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-226	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	6"	6"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-51	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-44	Sheet	Neoprene	Fabric-Reinforced	70A	1/16"	36"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-227	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	6"	6"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-52	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-45	Sheet	Neoprene	Fabric-Reinforced	70A	1/8"	36"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-229	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	6"	6"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-54	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-47	Sheet	Neoprene	Fabric-Reinforced	70A	1/4"	36"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-238	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	4 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-241	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-244	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	6 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-247	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	7 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-250	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	8 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-253	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	9 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-205	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	10 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-232	Roll	Neoprene	Fabric-Reinforced	70A	1/16"	36"	50 ft.	Black	Plain	Smooth	ASTM D2000 BC 710
BULK-RS-NFR70-239	Roll	Neoprene	Fabric-Reinforced	70A	1/8"	36"	4 ft.	Black	Plain	Smooth	ASTM D2000 BC 710