


Ultra Strength Buna-N Rubber

This formulation is stronger and more durable than both Standard and High Strength Buna-N for the most demanding applications. Buna-N is ideal for oils, greases, fuels, and petroleum applications. It also works well with water and mild chemicals and has excellent physical properties making it tough and durable.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-HUS50-274	Strip	Buna-N	Ultra Strength	50A	1/32"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-290	Strip	Buna-N	Ultra Strength	50A	1/32"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-306	Strip	Buna-N	Ultra Strength	50A	1/32"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-275	Strip	Buna-N	Ultra Strength	50A	1/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-291	Strip	Buna-N	Ultra Strength	50A	1/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-307	Strip	Buna-N	Ultra Strength	50A	1/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-276	Strip	Buna-N	Ultra Strength	50A	3/32"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-292	Strip	Buna-N	Ultra Strength	50A	3/32"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-308	Strip	Buna-N	Ultra Strength	50A	3/32"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-277	Strip	Buna-N	Ultra Strength	50A	1/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-293	Strip	Buna-N	Ultra Strength	50A	1/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS50-309	Strip	Buna-N	Ultra Strength	50A	1/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 517
BULK-RS-HUS60-274	Strip	Buna-N	Ultra Strength	60A	1/32"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-290	Strip	Buna-N	Ultra Strength	60A	1/32"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-306	Strip	Buna-N	Ultra Strength	60A	1/32"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-275	Strip	Buna-N	Ultra Strength	60A	1/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-291	Strip	Buna-N	Ultra Strength	60A	1/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-307	Strip	Buna-N	Ultra Strength	60A	1/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-276	Strip	Buna-N	Ultra Strength	60A	3/32"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-292	Strip	Buna-N	Ultra Strength	60A	3/32"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-308	Strip	Buna-N	Ultra Strength	60A	3/32"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-277	Strip	Buna-N	Ultra Strength	60A	1/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-293	Strip	Buna-N	Ultra Strength	60A	1/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-309	Strip	Buna-N	Ultra Strength	60A	1/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-278	Strip	Buna-N	Ultra Strength	60A	3/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-294	Strip	Buna-N	Ultra Strength	60A	3/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-310	Strip	Buna-N	Ultra Strength	60A	3/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-279	Strip	Buna-N	Ultra Strength	60A	1/4"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-295	Strip	Buna-N	Ultra Strength	60A	1/4"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-311	Strip	Buna-N	Ultra Strength	60A	1/4"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-280	Strip	Buna-N	Ultra Strength	60A	3/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-296	Strip	Buna-N	Ultra Strength	60A	3/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-312	Strip	Buna-N	Ultra Strength	60A	3/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-281	Strip	Buna-N	Ultra Strength	60A	1/2"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-297	Strip	Buna-N	Ultra Strength	60A	1/2"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS60-313	Strip	Buna-N	Ultra Strength	60A	1/2"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 617
BULK-RS-HUS70-274	Strip	Buna-N	Ultra Strength	70A	1/32"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-290	Strip	Buna-N	Ultra Strength	70A	1/32"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-306	Strip	Buna-N	Ultra Strength	70A	1/32"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-275	Strip	Buna-N	Ultra Strength	70A	1/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-291	Strip	Buna-N	Ultra Strength	70A	1/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-307	Strip	Buna-N	Ultra Strength	70A	1/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-276	Strip	Buna-N	Ultra Strength	70A	3/32"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-292	Strip	Buna-N	Ultra Strength	70A	3/32"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-308	Strip	Buna-N	Ultra Strength	70A	3/32"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-277	Strip	Buna-N	Ultra Strength	70A	1/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-293	Strip	Buna-N	Ultra Strength	70A	1/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-309	Strip	Buna-N	Ultra Strength	70A	1/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-278	Strip	Buna-N	Ultra Strength	70A	3/16"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-294	Strip	Buna-N	Ultra Strength	70A	3/16"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-310	Strip	Buna-N	Ultra Strength	70A	3/16"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-279	Strip	Buna-N	Ultra Strength	70A	1/4"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-295	Strip	Buna-N	Ultra Strength	70A	1/4"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-311	Strip	Buna-N	Ultra Strength	70A	1/4"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-280	Strip	Buna-N	Ultra Strength	70A	3/8"	2"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-296	Strip	Buna-N	Ultra Strength	70A	3/8"	4"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717
BULK-RS-HUS70-312	Strip	Buna-N	Ultra Strength	70A	3/8"	6"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 717