


Weather Resistant EPDM Rubber

EPDM Rubber

EPDM is ideal for use outdoors and has excellent resistance to weather. It is particularly well suited for use in applications with steam and water.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-E60-77	Strip	EPDM	Standard	60A	1/32"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-86	Strip	EPDM	Standard	60A	1/32"	3/8"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-78	Strip	EPDM	Standard	60A	1/32"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-79	Strip	EPDM	Standard	60A	1/32"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-80	Strip	EPDM	Standard	60A	1/32"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-82	Strip	EPDM	Standard	60A	1/32"	1-1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-84	Strip	EPDM	Standard	60A	1/32"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-419	Strip	EPDM	Standard	60A	1/32"	3"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-425	Strip	EPDM	Standard	60A	1/32"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-431	Strip	EPDM	Standard	60A	1/32"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-57	Strip	EPDM	Standard	60A	1/16"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-66	Strip	EPDM	Standard	60A	1/16"	3/8"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-58	Strip	EPDM	Standard	60A	1/16"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-59	Strip	EPDM	Standard	60A	1/16"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-60	Strip	EPDM	Standard	60A	1/16"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-62	Strip	EPDM	Standard	60A	1/16"	1-1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-64	Strip	EPDM	Standard	60A	1/16"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-420	Strip	EPDM	Standard	60A	1/16"	3"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-426	Strip	EPDM	Standard	60A	1/16"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-432	Strip	EPDM	Standard	60A	1/16"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-400	Strip	EPDM	Standard	60A	3/32"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-401	Strip	EPDM	Standard	60A	3/32"	3/8"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-402	Strip	EPDM	Standard	60A	3/32"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-409	Strip	EPDM	Standard	60A	3/32"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-410	Strip	EPDM	Standard	60A	3/32"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-411	Strip	EPDM	Standard	60A	3/32"	1-1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-412	Strip	EPDM	Standard	60A	3/32"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-421	Strip	EPDM	Standard	60A	3/32"	3"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-427	Strip	EPDM	Standard	60A	3/32"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-433	Strip	EPDM	Standard	60A	3/32"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-97	Strip	EPDM	Standard	60A	1/8"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-106	Strip	EPDM	Standard	60A	1/8"	3/8"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-98	Strip	EPDM	Standard	60A	1/8"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-99	Strip	EPDM	Standard	60A	1/8"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-100	Strip	EPDM	Standard	60A	1/8"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-102	Strip	EPDM	Standard	60A	1/8"	1-1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-104	Strip	EPDM	Standard	60A	1/8"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-422	Strip	EPDM	Standard	60A	1/8"	3"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-428	Strip	EPDM	Standard	60A	1/8"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-434	Strip	EPDM	Standard	60A	1/8"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-107	Strip	EPDM	Standard	60A	3/16"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-116	Strip	EPDM	Standard	60A	3/16"	3/8"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-108	Strip	EPDM	Standard	60A	3/16"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-109	Strip	EPDM	Standard	60A	3/16"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-110	Strip	EPDM	Standard	60A	3/16"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-112	Strip	EPDM	Standard	60A	3/16"	1-1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-114	Strip	EPDM	Standard	60A	3/16"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-423	Strip	EPDM	Standard	60A	3/16"	3"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-429	Strip	EPDM	Standard	60A	3/16"	4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-435	Strip	EPDM	Standard	60A	3/16"	6"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-87	Strip	EPDM	Standard	60A	1/4"	1/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-96	Strip	EPDM	Standard	60A	1/4"	3/8"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-88	Strip	EPDM	Standard	60A	1/4"	1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-89	Strip	EPDM	Standard	60A	1/4"	3/4"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-90	Strip	EPDM	Standard	60A	1/4"	1"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-92	Strip	EPDM	Standard	60A	1/4"	1-1/2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-94	Strip	EPDM	Standard	60A	1/4"	2"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607
BULK-RS-E60-424	Strip	EPDM	Standard	60A	1/4"	3"	10 ft.	Black	Plain	Smooth	ASTM D2000 BA 607