

# Ball-Point Hexagonal Wrenches

Stock 1,057 Items

4-723



Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items**

## Ball-Point Hexagonal Bar Wrench




- Features**
- Flat corners at the tip of the hexagonal bar are chamfered equally on each side. Easier to insert into the hexagon socket hole, and the chamfer angle is considered to be in close contact with "the corner edge" of the hexagon hole base.
  - The hardness is HRC54 to 59.
  - You can turn the screw from the angle of 25° maximum.
- Materials**
- Chrome Vanadium Steel
- Origin**
- Japan



### Ball-point Type

- Work is quick even in narrow places!
- Make sure to engage with the screw thread!



Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
125-2666	GXB-15	¥ 463	¥ 500	1.5	14	50	10	1
125-2674	GXB-20	¥ 463	¥ 500	2.0	16	56	10	2
125-2682	GXB-25	¥ 472	¥ 510	2.5	18	63	10	3
125-2691	GXB-30	¥ 490	¥ 530	3.0	20	71	10	5
125-2704	GXB-40	¥ 509	¥ 550	4.0	22	80	10	10
125-2712	GXB-50	¥ 546	¥ 590	5.0	25	90	10	18
125-2721	GXB-60	¥ 630	¥ 680	6.0	28	100	10	30
125-2739	GXB-80	¥ 787	¥ 850	8.0	32	112	10	62
125-2747	GXB-100	¥1,037	¥1,120	10.0	36	125	10	110
125-2755	GXB-120	¥2,166	¥2,340	12.0	40	140	3	176
125-2763	GXB-140	¥2,546	¥2,750	14.0	45	160	3	280

Set Accessories • Holder

Order Unit: 1 Set

(Price revision date: Jan, 2015)

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
125-2348	GXB-7S	¥3,684	¥3,980	1.5, 2, 2.5, 3, 4, 5, 6	7	10	100
125-2372	GXB-8S	¥4,999	¥5,400	1.5, 2, 2.5, 3, 4, 5, 6, 8	8	5	140
125-2381	GXB-9S	¥5,453	¥5,890	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	9	5	280



Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

## Ball-Point Hexagonal Wrenches (long type)




- Features**
- Easily capture the screws, quickly and comfortably to enter and save useless time.
  - The hardness is HRC54 to 59.
  - You can turn the screw from the angle of 25° maximum.
- Materials**
- Chrome Vanadium Steel
- Origin**
- Japan



### Ball-point Type

- Work is quick even in narrow places!
- Make sure to engage with the screw thread!



Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Opposite Side Dimension (mm)	Length Excl. Head (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
125-3158	GXBL-15	¥ 528	¥ 570	1.5	14	90	10	2
125-3166	GXBL-20	¥ 546	¥ 590	2.0	16	100	10	3
125-3174	GXBL-25	¥ 573	¥ 620	2.5	18	112	10	5
125-3182	GXBL-30	¥ 593	¥ 640	3.0	20	126	10	9
125-3191	GXBL-40	¥ 630	¥ 680	4.0	23	142	10	16
125-3204	GXBL-50	¥ 731	¥ 790	5.0	28	160	10	30
125-3212	GXBL-60	¥ 926	¥1,000	6.0	32	180	10	50
125-3221	GXBL-80	¥1,166	¥1,260	8.0	36	200	10	100
125-3239	GXBL-100	¥1,703	¥1,840	10.0	40	224	10	178
125-3247	GXBL-120	¥2,620	¥2,830	12.0	45	250	3	290
125-3255	GXBL-140	¥3,323	¥3,590	14.0	56	280	3	448
488-5813	GXBL-170	¥5,656	¥6,110	17.0	63	320	5	754
488-5821	GXBL-190	¥7,276	¥7,860	19.0	70	360	5	1055

Set Accessories • Holder

Order Unit: 1 Set

(Price revision date: Jan, 2015)

Order Code	Item No.	Price (per set)	MSRP (per set)	Set Contents (mm)	Set Contents (piece)	SPQ (set)	Weight (g/set)
125-2968	GXBL-7S	¥4,481	¥4,840	1.5, 2, 2.5, 3, 4, 5, 6	7	10	140
125-2976	GXBL-8S	¥5,832	¥6,300	1.5, 2, 2.5, 3, 4, 5, 6, 8	8	5	252
125-2984	GXBL-9S	¥7,322	¥7,910	1.5, 2, 2.5, 3, 4, 5, 6, 8, 10	9	5	450

Contact us:0120-509-849 <http://www.orange-book.com/>

Screwdrivers-Hexagonal Wrenches

Grip Screwdrivers

Screwdrivers with Plastic Handle

Stubby Screwdrivers

Screwdrivers with Wood Handle

Precision Screwdrivers

Electric Detection Screwdrivers

Interchangeable Screwdrivers

Ratchet Screwdrivers

Offset Ratchet Screwdrivers

Socket Screwdrivers

Impact Drivers (Manual Type)

Hexagon Driver

Hex Lobe Screwdrivers

Special-Purpose Screwdrivers

Ball-Point Hexagonal Wrenches

Hexagonal Wrenches

Hex Lobe Wrenches