


Air Impermeable Butyl Rubber

Butyl Rubber

Butyl Rubber is well known for its air impermeability and is often used in airtight applications. It is also known as Isobutylene Isoprene.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-BTL60-13	Strip	Butyl	Standard	60A	1/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-16	Strip	Butyl	Standard	60A	1/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-19	Strip	Butyl	Standard	60A	1/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-14	Strip	Butyl	Standard	60A	1/8"	2"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-17	Strip	Butyl	Standard	60A	1/8"	4"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-20	Strip	Butyl	Standard	60A	1/8"	6"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-15	Strip	Butyl	Standard	60A	1/4"	2"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-18	Strip	Butyl	Standard	60A	1/4"	4"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-21	Strip	Butyl	Standard	60A	1/4"	6"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-31	Strip	Butyl	Standard	60A	1/16"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-34	Strip	Butyl	Standard	60A	1/16"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-37	Strip	Butyl	Standard	60A	1/16"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-32	Strip	Butyl	Standard	60A	1/8"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-35	Strip	Butyl	Standard	60A	1/8"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-38	Strip	Butyl	Standard	60A	1/8"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-33	Strip	Butyl	Standard	60A	1/4"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-36	Strip	Butyl	Standard	60A	1/4"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-39	Strip	Butyl	Standard	60A	1/4"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-4	Sheet	Butyl	Standard	60A	1/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-7	Sheet	Butyl	Standard	60A	1/16"	12"	24"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-10	Sheet	Butyl	Standard	60A	1/16"	12"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-41	Sheet	Butyl	Standard	60A	1/16"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-5	Sheet	Butyl	Standard	60A	1/8"	12"	12"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-8	Sheet	Butyl	Standard	60A	1/8"	12"	24"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-11	Sheet	Butyl	Standard	60A	1/8"	12"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-44	Sheet	Butyl	Standard	60A	1/8"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-6	Sheet	Butyl	Standard	60A	1/4"	12"	12"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-9	Sheet	Butyl	Standard	60A	1/4"	12"	24"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-12	Sheet	Butyl	Standard	60A	1/4"	12"	36"	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-42	Sheet	Butyl	Standard	60A	1/4"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-22	Sheet	Butyl	Standard	60A	1/16"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-25	Sheet	Butyl	Standard	60A	1/16"	12"	24"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-28	Sheet	Butyl	Standard	60A	1/16"	12"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-23	Sheet	Butyl	Standard	60A	1/8"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-26	Sheet	Butyl	Standard	60A	1/8"	12"	24"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-29	Sheet	Butyl	Standard	60A	1/8"	12"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-24	Sheet	Butyl	Standard	60A	1/4"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-27	Sheet	Butyl	Standard	60A	1/4"	12"	24"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-30	Sheet	Butyl	Standard	60A	1/4"	12"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-40	Roll	Butyl	Standard	60A	1/16"	36"	10 ft.	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-47	Roll	Butyl	Standard	60A	1/16"	36"	25 ft.	Black	Plain	Smooth	ASTM D2000 M1AA 607
BULK-RS-BTL60-1	Roll	Butyl	Standard	60A	1/16"	36"	150 ft.	Black	Plain	Smooth	ASTM D2000 M1AA 607