

Ring Pliers

The number next to the logo mark indicates items in stock for each brand.

Pliers · Cutting Pliers · Nippers

Pliers

Nose Pliers

Machine Screw Pliers

Ring Pliers

Snap Ring Pliers

Pliers

Crimping Pliers

Radio Pliers

Multi Tools

Nippers

Electrical Engineering Nippers

Electrical and Electronic Nippers

Plastic Nippers

Stainless Steel Nippers

Heat Nippers

TRUSCO



Stock 38,650 Items

Versatile Type Double Ring Pliers

- Features** • The ring opens in a single operation. (PAT.P)
Specs • Cutting performance: Φ 1.0 for iron wire, Φ 1.8 for copper wire
 • Polished gloss finish.
Materials • Carbon Steel (S58C) **Origin** • Japan



Tip Shape



Tip Shape



Tip Shape



TRP-15S



TRP-20H



TRP-40L




Example



Example



Example



Adaptation Ring Size

Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Working Wire Diameter Range (mm)	Adaptation Ring Size L (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
408-9014	TRP-15S	¥2,555	¥2,760	0.5 to 1.0	6 to 15	155	6	125
408-9031	TRP-20H	¥2,379	¥2,570	1.2 to 1.8	12 to 20	145	6	125
408-9022	TRP-40L	¥2,555	¥2,760	1.0 to 1.5	15 to 40	150	6	125

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO




Stock 38,650 Items

Double Ring Pliers


- Features** • The ring opens in a single operation. (PAT.P)
Specs • Cutting performance: Φ 1.0 for iron wire, Φ 1.8 for copper wire
 • Polished gloss finish.
Origin • Japan



Tip Shape



TRP-6



Adaptation Ring Size



Example

Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Working Wire Diameter Range (mm)	Adaptation Ring Size L (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
280-9885	TRP-6	¥2,222	¥2,400	0.5 to 1.5	3 to 8	155	6	125
280-9893	TRP-11	¥2,268	¥2,450	1.0 to 2.5	8 to 30	150	6	125

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

E Ring Pliers


- Features** • The optimum pliers for detaching the E ring.
 • Work can be done speedy.
 • Polished gloss finish.
Materials • Carbon Steel (S58C)
Origin • Japan



Tip Shape



TEP-5



Adaptation E Ring



Example

Order Unit: 1 Piece

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Adaptation E Ring Size (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
280-9869	TEP-5	¥1,851	¥2,000	3 to 5	150	6	120
280-9877	TEP-8	¥1,898	¥2,050	6 to 8	145	6	120

Contact us:0120-509-849 <http://www.orange-book.com/>