


# Chemical Resistant Hypalon Rubber

## Hypalon Rubber

Hypalon Rubber is noted for its good chemical and water resistance and is often used as an outside liner for protection. Hypalon can be used as an alternative to Neoprene.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-HPN60-21	Strip	Hypalon	Standard	60A	1/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-26	Strip	Hypalon	Standard	60A	1/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-31	Strip	Hypalon	Standard	60A	1/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-22	Strip	Hypalon	Standard	60A	3/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-27	Strip	Hypalon	Standard	60A	3/32"	4"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-32	Strip	Hypalon	Standard	60A	3/32"	6"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-23	Strip	Hypalon	Standard	60A	1/8"	2"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-28	Strip	Hypalon	Standard	60A	1/8"	4"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-33	Strip	Hypalon	Standard	60A	1/8"	6"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-24	Strip	Hypalon	Standard	60A	3/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-29	Strip	Hypalon	Standard	60A	3/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-34	Strip	Hypalon	Standard	60A	3/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-25	Strip	Hypalon	Standard	60A	1/4"	2"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-30	Strip	Hypalon	Standard	60A	1/4"	4"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-35	Strip	Hypalon	Standard	60A	1/4"	6"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-48	Strip	Hypalon	Standard	60A	1/16"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-53	Strip	Hypalon	Standard	60A	1/16"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-58	Strip	Hypalon	Standard	60A	1/16"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-49	Strip	Hypalon	Standard	60A	3/32"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-54	Strip	Hypalon	Standard	60A	3/32"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-59	Strip	Hypalon	Standard	60A	3/32"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-50	Strip	Hypalon	Standard	60A	1/8"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-55	Strip	Hypalon	Standard	60A	1/8"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-60	Strip	Hypalon	Standard	60A	1/8"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-51	Strip	Hypalon	Standard	60A	3/16"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-56	Strip	Hypalon	Standard	60A	3/16"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-61	Strip	Hypalon	Standard	60A	3/16"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-52	Strip	Hypalon	Standard	60A	1/4"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-57	Strip	Hypalon	Standard	60A	1/4"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-62	Strip	Hypalon	Standard	60A	1/4"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-6	Sheet	Hypalon	Standard	60A	1/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-11	Sheet	Hypalon	Standard	60A	1/16"	12"	24"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-16	Sheet	Hypalon	Standard	60A	1/16"	12"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-64	Sheet	Hypalon	Standard	60A	1/16"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-7	Sheet	Hypalon	Standard	60A	3/32"	12"	12"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-12	Sheet	Hypalon	Standard	60A	3/32"	12"	24"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-17	Sheet	Hypalon	Standard	60A	3/32"	12"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-8	Sheet	Hypalon	Standard	60A	1/8"	12"	12"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-13	Sheet	Hypalon	Standard	60A	1/8"	12"	24"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-18	Sheet	Hypalon	Standard	60A	1/8"	12"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-68	Sheet	Hypalon	Standard	60A	1/8"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-9	Sheet	Hypalon	Standard	60A	3/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-14	Sheet	Hypalon	Standard	60A	3/16"	12"	24"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-19	Sheet	Hypalon	Standard	60A	3/16"	12"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-10	Sheet	Hypalon	Standard	60A	1/4"	12"	12"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-15	Sheet	Hypalon	Standard	60A	1/4"	12"	24"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-20	Sheet	Hypalon	Standard	60A	1/4"	12"	36"	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-66	Sheet	Hypalon	Standard	60A	1/4"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-36	Sheet	Hypalon	Standard	60A	1/16"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-40	Sheet	Hypalon	Standard	60A	1/16"	12"	24"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-43	Sheet	Hypalon	Standard	60A	1/16"	12"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-44	Sheet	Hypalon	Standard	60A	3/32"	12"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-37	Sheet	Hypalon	Standard	60A	1/8"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-41	Sheet	Hypalon	Standard	60A	1/8"	12"	24"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-45	Sheet	Hypalon	Standard	60A	1/8"	12"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE
BULK-RS-HPN60-38	Sheet	Hypalon	Standard	60A	3/16"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 1CE