


CPVC Plastic

CPVC can withstand higher temperatures compared to PVC Type 1, while retaining chemical-resistant properties.



Part Number	Shape	Material	Grade	Thickness	Width	Length	Color	Clarity	Backing Type
PS-CPVC-31	Bar	CPVC	Standard	1/16"	1/2"	12"	Gray	Opaque	Plain
PS-CPVC-59	Bar	CPVC	Standard	1/8"	1/2"	12"	Gray	Opaque	Plain
PS-CPVC-87	Bar	CPVC	Standard	1/4"	1/2"	12"	Gray	Opaque	Plain
PS-CPVC-115	Bar	CPVC	Standard	1/2"	1/2"	12"	Gray	Opaque	Plain
PS-CPVC-32	Bar	CPVC	Standard	1/16"	1/2"	24"	Gray	Opaque	Plain
PS-CPVC-60	Bar	CPVC	Standard	1/8"	1/2"	24"	Gray	Opaque	Plain
PS-CPVC-88	Bar	CPVC	Standard	1/4"	1/2"	24"	Gray	Opaque	Plain
PS-CPVC-116	Bar	CPVC	Standard	1/2"	1/2"	24"	Gray	Opaque	Plain
PS-CPVC-33	Bar	CPVC	Standard	1/16"	1/2"	36"	Gray	Opaque	Plain
PS-CPVC-61	Bar	CPVC	Standard	1/8"	1/2"	36"	Gray	Opaque	Plain
PS-CPVC-89	Bar	CPVC	Standard	1/4"	1/2"	36"	Gray	Opaque	Plain
PS-CPVC-117	Bar	CPVC	Standard	1/2"	1/2"	36"	Gray	Opaque	Plain
PS-CPVC-34	Bar	CPVC	Standard	1/16"	1/2"	48"	Gray	Opaque	Plain
PS-CPVC-62	Bar	CPVC	Standard	1/8"	1/2"	48"	Gray	Opaque	Plain
PS-CPVC-90	Bar	CPVC	Standard	1/4"	1/2"	48"	Gray	Opaque	Plain
PS-CPVC-118	Bar	CPVC	Standard	1/2"	1/2"	48"	Gray	Opaque	Plain
PS-CPVC-35	Bar	CPVC	Standard	1/16"	1"	12"	Gray	Opaque	Plain
PS-CPVC-63	Bar	CPVC	Standard	1/8"	1"	12"	Gray	Opaque	Plain
PS-CPVC-91	Bar	CPVC	Standard	1/4"	1"	12"	Gray	Opaque	Plain
PS-CPVC-119	Bar	CPVC	Standard	1/2"	1"	12"	Gray	Opaque	Plain
PS-CPVC-143	Bar	CPVC	Standard	1"	1"	12"	Gray	Opaque	Plain
PS-CPVC-36	Bar	CPVC	Standard	1/16"	1"	24"	Gray	Opaque	Plain
PS-CPVC-64	Bar	CPVC	Standard	1/8"	1"	24"	Gray	Opaque	Plain
PS-CPVC-92	Bar	CPVC	Standard	1/4"	1"	24"	Gray	Opaque	Plain
PS-CPVC-120	Bar	CPVC	Standard	1/2"	1"	24"	Gray	Opaque	Plain
PS-CPVC-144	Bar	CPVC	Standard	1"	1"	24"	Gray	Opaque	Plain
PS-CPVC-37	Bar	CPVC	Standard	1/16"	1"	36"	Gray	Opaque	Plain
PS-CPVC-65	Bar	CPVC	Standard	1/8"	1"	36"	Gray	Opaque	Plain
PS-CPVC-93	Bar	CPVC	Standard	1/4"	1"	36"	Gray	Opaque	Plain
PS-CPVC-121	Bar	CPVC	Standard	1/2"	1"	36"	Gray	Opaque	Plain
PS-CPVC-145	Bar	CPVC	Standard	1"	1"	36"	Gray	Opaque	Plain
PS-CPVC-38	Bar	CPVC	Standard	1/16"	1"	48"	Gray	Opaque	Plain
PS-CPVC-66	Bar	CPVC	Standard	1/8"	1"	48"	Gray	Opaque	Plain
PS-CPVC-94	Bar	CPVC	Standard	1/4"	1"	48"	Gray	Opaque	Plain
PS-CPVC-122	Bar	CPVC	Standard	1/2"	1"	48"	Gray	Opaque	Plain
PS-CPVC-146	Bar	CPVC	Standard	1"	1"	48"	Gray	Opaque	Plain
PS-CPVC-39	Bar	CPVC	Standard	1/16"	1-1/2"	12"	Gray	Opaque	Plain
PS-CPVC-67	Bar	CPVC	Standard	1/8"	1-1/2"	12"	Gray	Opaque	Plain
PS-CPVC-95	Bar	CPVC	Standard	1/4"	1-1/2"	12"	Gray	Opaque	Plain
PS-CPVC-123	Bar	CPVC	Standard	1/2"	1-1/2"	12"	Gray	Opaque	Plain
PS-CPVC-147	Bar	CPVC	Standard	1"	1-1/2"	12"	Gray	Opaque	Plain
PS-CPVC-40	Bar	CPVC	Standard	1/16"	1-1/2"	24"	Gray	Opaque	Plain
PS-CPVC-68	Bar	CPVC	Standard	1/8"	1-1/2"	24"	Gray	Opaque	Plain
PS-CPVC-96	Bar	CPVC	Standard	1/4"	1-1/2"	24"	Gray	Opaque	Plain
PS-CPVC-124	Bar	CPVC	Standard	1/2"	1-1/2"	24"	Gray	Opaque	Plain
PS-CPVC-148	Bar	CPVC	Standard	1"	1-1/2"	24"	Gray	Opaque	Plain
PS-CPVC-41	Bar	CPVC	Standard	1/16"	1-1/2"	36"	Gray	Opaque	Plain
PS-CPVC-69	Bar	CPVC	Standard	1/8"	1-1/2"	36"	Gray	Opaque	Plain
PS-CPVC-97	Bar	CPVC	Standard	1/4"	1-1/2"	36"	Gray	Opaque	Plain
PS-CPVC-125	Bar	CPVC	Standard	1/2"	1-1/2"	36"	Gray	Opaque	Plain
PS-CPVC-149	Bar	CPVC	Standard	1"	1-1/2"	36"	Gray	Opaque	Plain
PS-CPVC-42	Bar	CPVC	Standard	1/16"	1-1/2"	48"	Gray	Opaque	Plain
PS-CPVC-70	Bar	CPVC	Standard	1/8"	1-1/2"	48"	Gray	Opaque	Plain
PS-CPVC-98	Bar	CPVC	Standard	1/4"	1-1/2"	48"	Gray	Opaque	Plain
PS-CPVC-126	Bar	CPVC	Standard	1/2"	1-1/2"	48"	Gray	Opaque	Plain
PS-CPVC-150	Bar	CPVC	Standard	1"	1-1/2"	48"	Gray	Opaque	Plain
PS-CPVC-43	Bar	CPVC	Standard	1/16"	2"	12"	Gray	Opaque	Plain
PS-CPVC-71	Bar	CPVC	Standard	1/8"	2"	12"	Gray	Opaque	Plain