


For Impact, Electric Screwdriver, see p. 5-77 to 119, 124 to 156. For Air Screwdriver, see p. 5-459 to 467



Stock 38,650 Items

## Mag Catch



TMC-GN

TMC-R



TMC-W



TMC-Y



TMCMB (mini)




TMCMB-OR (mini)

- Features
- Optimum for magnetic force up of screwdriver and electric bit.
  - Catches the screw firmly, avoiding to drop screw.
- Origin
- China

### Warning

- Can not be used for round shaft bit for electric drive or bit less than 65mm.

(installation example)



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Size (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
419-9901	TMC-GN	¥407	¥440	Φ6.35, Hexagon Bit 6.35	27	12	5
419-9910	TMC-R	¥407	¥440	Φ6.35, Hexagon Bit 6.35	27	12	5
419-9928	TMC-W	¥407	¥440	Φ6.35, Hexagon Bit 6.35	27	12	5
419-9936	TMC-Y	¥407	¥440	Φ6.35, Hexagon Bit 6.35	27	12	5

## Mag Catch Mini

Order Unit: 1 Piece

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible Size (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
478-9369	TMCMB	¥407	¥440	Φ4.5 to 5.5	19	20	4.5
478-9377	TMCMB-OR	¥407	¥440	Φ4.5 to 5.5	19	20	4.5

Contact us: 0120-509-849 <http://www.orange-book.com/>




Stock 38,650 Items

## Magnet/Screw Catch



TMB-2065

- Features
- The screw always stops constantly against the surface.
  - Since the screw lock is completely locked with the bit with the automatic lock function, the output dimension of the bit does not change when using the impact screwdriver.
  - Even with long screw, you can grab firmly with a powerful magnet, and you can easily screw it.
- Specs
- Shank Diameter: 6.35mm
- Set Contents
- Double End Drill Bit ΦNo. 2 x 65 Bit with 1 Piece
- Origin
- Japan



Order Unit: 1 Set

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per set)	MSRP (per set)	Total Length (mm)	SPQ (set)	Weight (g/set)
270-9511	TMB-2065	¥1,018	¥1,100	65	12	38

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

## Mag Catch (magnetization and demagnetizer)



TMC-8

- Features
- Magnetizable and demagnetizable.
  - The round shaft can be up to 8mm and the hexagonal shaft up to 6.35mm.
- Origin
- Japan



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	SPQ (piece)	Weight (g)
449-9662	TMC-8	¥463	¥500	48	10	29

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 1,489 Items

## "Magnetic Screw Catcher"



NMC-2P



NMC-2P (contains 2 pieces)

- Features
- Attach to the bit or screwdriver for magnetizing with a powerful magnetic force.
  - A powerful magnet firmly catches long coarse thread screw as well.
  - Magnetizable and demagnetizable.
- Origin
- China

### Warning

- It is not possible to completely remove magnetization.
- Can not be used for round shaft bit for electric drive or bit less than 6mm.



Order Unit: 1 Bag

VESSEL CO.,INC.

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Compatible Size (mm)	Total Length (mm)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
810-6963	NMC-2P	¥634	—	Φ6.35, Hexagon Bit 6.35	27	2	10	11

Contact us: 0120-999-914 <http://www.vessel.co.jp/>