


FDA Silicone Foam

Silicone displays excellent resistance to high and low temperatures, compression set, chemicals and weather. Applications include gaskets, heat shields, fire stops, cushions, and insulation for a wide variety of applications. This Silicone Foam is made of FDA materials and is lighter and more resilient than most Silicone foams. It is also UL listed for flame retardance.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture	Specs Met
ZUSASSR-FDA-1	Strip	Closed Cell	Silicone	Food	1/16"	1/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-4	Strip	Closed Cell	Silicone	Food	1/16"	3/8"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-8	Strip	Closed Cell	Silicone	Food	1/16"	1/2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-13	Strip	Closed Cell	Silicone	Food	1/16"	3/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-18	Strip	Closed Cell	Silicone	Food	1/16"	1"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-23	Strip	Closed Cell	Silicone	Food	1/16"	2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-2	Strip	Closed Cell	Silicone	Food	1/8"	1/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-5	Strip	Closed Cell	Silicone	Food	1/8"	3/8"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-9	Strip	Closed Cell	Silicone	Food	1/8"	1/2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-14	Strip	Closed Cell	Silicone	Food	1/8"	3/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-19	Strip	Closed Cell	Silicone	Food	1/8"	1"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-24	Strip	Closed Cell	Silicone	Food	1/8"	2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-3	Strip	Closed Cell	Silicone	Food	1/4"	1/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-6	Strip	Closed Cell	Silicone	Food	1/4"	3/8"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-10	Strip	Closed Cell	Silicone	Food	1/4"	1/2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-15	Strip	Closed Cell	Silicone	Food	1/4"	3/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-20	Strip	Closed Cell	Silicone	Food	1/4"	1"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-25	Strip	Closed Cell	Silicone	Food	1/4"	2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-7	Strip	Closed Cell	Silicone	Food	3/8"	3/8"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-11	Strip	Closed Cell	Silicone	Food	3/8"	1/2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-16	Strip	Closed Cell	Silicone	Food	3/8"	3/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-21	Strip	Closed Cell	Silicone	Food	3/8"	1"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-26	Strip	Closed Cell	Silicone	Food	3/8"	2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-12	Strip	Closed Cell	Silicone	Food	1/2"	1/2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-17	Strip	Closed Cell	Silicone	Food	1/2"	3/4"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-22	Strip	Closed Cell	Silicone	Food	1/2"	1"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-27	Strip	Closed Cell	Silicone	Food	1/2"	2"	6 ft.	Gray	Medium (9 - 13 psi)	High Temperature Adhesive	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-101	Sheet	Closed Cell	Silicone	Food	1/16"	12"	12"	Gray	Medium (9 - 13 psi)	Plain	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-106	Sheet	Closed Cell	Silicone	Food	1/16"	12"	24"	Gray	Medium (9 - 13 psi)	Plain	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-201	Sheet	Closed Cell	Silicone	Food	1/16"	12"	12 ft.	Gray	Medium (9 - 13 psi)	Plain	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-102	Sheet	Closed Cell	Silicone	Food	1/8"	12"	12"	Gray	Medium (9 - 13 psi)	Plain	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1
ZUSASSR-FDA-107	Sheet	Closed Cell	Silicone	Food	1/8"	12"	24"	Gray	Medium (9 - 13 psi)	Plain	Ultra Smooth	ASTM D1056 2D3, UL 94 V-0, UL 94 HF-1