

Low Compression Set Silicone Foam

Silicone displays excellent resistance to high and low temperatures, compression set, chemicals and weather. Applications include gaskets, heat shields, fire stops, cushions, and insulation for a wide variety of applications. This Silicone bounces back to its shape after long term or repeated compression. It is an excellent material for use in creating devices, equipment, and components that must last for years.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture	Specs Met
ZUSA12CR10480-1	Strip	Closed Cell	Silicone	Low Compression Set	1/16"	1/2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-7	Strip	Closed Cell	Silicone	Low Compression Set	1/16"	1"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-13	Strip	Closed Cell	Silicone	Low Compression Set	1/16"	2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-19	Strip	Closed Cell	Silicone	Low Compression Set	1/16"	4"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-25	Strip	Closed Cell	Silicone	Low Compression Set	1/16"	6"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-2	Strip	Closed Cell	Silicone	Low Compression Set	1/8"	1/2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-8	Strip	Closed Cell	Silicone	Low Compression Set	1/8"	1"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-14	Strip	Closed Cell	Silicone	Low Compression Set	1/8"	2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-20	Strip	Closed Cell	Silicone	Low Compression Set	1/8"	4"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-26	Strip	Closed Cell	Silicone	Low Compression Set	1/8"	6"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-3	Strip	Closed Cell	Silicone	Low Compression Set	3/16"	1/2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-9	Strip	Closed Cell	Silicone	Low Compression Set	3/16"	1"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-15	Strip	Closed Cell	Silicone	Low Compression Set	3/16"	2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-21	Strip	Closed Cell	Silicone	Low Compression Set	3/16"	4"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-27	Strip	Closed Cell	Silicone	Low Compression Set	3/16"	6"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-4	Strip	Closed Cell	Silicone	Low Compression Set	1/4"	1/2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-10	Strip	Closed Cell	Silicone	Low Compression Set	1/4"	1"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-16	Strip	Closed Cell	Silicone	Low Compression Set	1/4"	2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-22	Strip	Closed Cell	Silicone	Low Compression Set	1/4"	4"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-28	Strip	Closed Cell	Silicone	Low Compression Set	1/4"	6"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-5	Strip	Closed Cell	Silicone	Low Compression Set	3/8"	1/2"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3
ZUSA12CR10480-11	Strip	Closed Cell	Silicone	Low Compression Set	3/8"	1"	36"	Brown	Medium (9 - 13 psi)	High Temperature Adhesive	Smooth	ASTM D1056 2D3