


Oil Resistant Buna-N/PVC Foam

Buna-N/PVC foam exhibits excellent impact absorption and good chemical resistance properties. Also known as crushed-cell foam, semi-closed foam is highly conformable like an open-cell foam but forms a tight seal and prevents air, water, and fluids from passing through it like a closed-cell foam.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture
ZUSA-CBPSR-64	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-73	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-86	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-103	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-65	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-74	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-87	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-104	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-66	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-75	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-88	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-105	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-67	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	1/4"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-76	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-89	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-106	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-77	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/8"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-90	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/8"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-107	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/8"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-78	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/2"	1/2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-91	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/2"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-108	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/2"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-92	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/4"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-109	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/4"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-93	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1"	1"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-110	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1"	2"	10 ft.	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-193	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-202	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-215	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-232	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-194	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-203	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-216	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-233	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-195	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-204	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-217	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-234	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/16"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-196	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	1/4"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-205	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-218	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-235	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/4"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-206	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/8"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-219	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/8"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-236	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/8"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-207	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/2"	1/2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-220	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/2"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-237	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1/2"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-221	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/4"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-238	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	3/4"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-222	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1"	1"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-239	Strip	Semi-Closed Cell	Buna-N/PVC	Standard	1"	2"	10 ft.	Black	Extra Soft	Acrylic Adhesive	Textured
ZUSA-CBPSR-28	Sheet	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	12"	12"	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-37	Sheet	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	12"	24"	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-55	Sheet	Semi-Closed Cell	Buna-N/PVC	Standard	1/16"	36"	36"	Black	Extra Soft	Plain	Textured
ZUSA-CBPSR-29	Sheet	Semi-Closed Cell	Buna-N/PVC	Standard	1/8"	12"	12"	Black	Extra Soft	Plain	Textured