


Buna-N MIL-Spec Rubber

This formulation of Buna-N is made to be compliant with military specifications. Buna-N is ideal for oils, greases, fuels, and petroleum applications. It also works well with water and mild chemicals and has excellent physical properties making it tough and durable.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-H40MIL-27	Sheet	Buna-N	Military	40A	1/64"	12"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-31	Sheet	Buna-N	Military	40A	1/64"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-36	Sheet	Buna-N	Military	40A	1/64"	12"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-39	Sheet	Buna-N	Military	40A	1/64"	12"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-44	Sheet	Buna-N	Military	40A	1/64"	36"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-48	Sheet	Buna-N	Military	40A	1/64"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-55	Sheet	Buna-N	Military	40A	1/64"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-61	Sheet	Buna-N	Military	40A	1/64"	36"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-32	Sheet	Buna-N	Military	40A	1/32"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-40	Sheet	Buna-N	Military	40A	1/32"	12"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-49	Sheet	Buna-N	Military	40A	1/32"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-62	Sheet	Buna-N	Military	40A	1/32"	36"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-28	Sheet	Buna-N	Military	40A	1/16"	12"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-33	Sheet	Buna-N	Military	40A	1/16"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-37	Sheet	Buna-N	Military	40A	1/16"	12"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-41	Sheet	Buna-N	Military	40A	1/16"	12"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-50	Sheet	Buna-N	Military	40A	1/16"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-56	Sheet	Buna-N	Military	40A	1/16"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-63	Sheet	Buna-N	Military	40A	1/16"	36"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-34	Sheet	Buna-N	Military	40A	3/32"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-42	Sheet	Buna-N	Military	40A	3/32"	12"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-45	Sheet	Buna-N	Military	40A	3/32"	36"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-51	Sheet	Buna-N	Military	40A	3/32"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-57	Sheet	Buna-N	Military	40A	3/32"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-29	Sheet	Buna-N	Military	40A	1/8"	12"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-38	Sheet	Buna-N	Military	40A	1/8"	12"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-43	Sheet	Buna-N	Military	40A	1/8"	12"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-52	Sheet	Buna-N	Military	40A	1/8"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-58	Sheet	Buna-N	Military	40A	1/8"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-64	Sheet	Buna-N	Military	40A	1/8"	36"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-35	Sheet	Buna-N	Military	40A	3/16"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-46	Sheet	Buna-N	Military	40A	3/16"	36"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-53	Sheet	Buna-N	Military	40A	3/16"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-59	Sheet	Buna-N	Military	40A	3/16"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-65	Sheet	Buna-N	Military	40A	3/16"	36"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H40MIL-30	Sheet	Buna-N	Military	40A	1/4"	12"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-47	Sheet	Buna-N	Military	40A	1/4"	36"	36"	Black	Plain	Smooth	MIL-R-3065D SB 410 F2
BULK-RS-H40MIL-54	Sheet	Buna-N	Military	40A	1/4"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 40
BULK-RS-H40MIL-60	Sheet	Buna-N	Military	40A	1/4"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG407
BULK-RS-H40MIL-66	Sheet	Buna-N	Military	40A	1/4"	36"	36"	Black	Plain	Smooth	MIL-R-2765
BULK-RS-H50MIL-21	Sheet	Buna-N	Military	50A	1/64"	12"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-32	Sheet	Buna-N	Military	50A	1/64"	12"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG507
BULK-RS-H50MIL-36	Sheet	Buna-N	Military	50A	1/64"	36"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-22	Sheet	Buna-N	Military	50A	1/32"	12"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-30	Sheet	Buna-N	Military	50A	1/32"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 50
BULK-RS-H50MIL-37	Sheet	Buna-N	Military	50A	1/32"	36"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-45	Sheet	Buna-N	Military	50A	1/32"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 50
BULK-RS-H50MIL-23	Sheet	Buna-N	Military	50A	1/16"	12"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-31	Sheet	Buna-N	Military	50A	1/16"	12"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 50
BULK-RS-H50MIL-33	Sheet	Buna-N	Military	50A	1/16"	12"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG507
BULK-RS-H50MIL-38	Sheet	Buna-N	Military	50A	1/16"	36"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-43	Sheet	Buna-N	Military	50A	1/16"	36"	36"	Black	Plain	Smooth	MIL-R-3065D SB 515 F2
BULK-RS-H50MIL-46	Sheet	Buna-N	Military	50A	1/16"	36"	36"	Black	Plain	Smooth	MIL-R-6855 Class 1 Grade 50
BULK-RS-H50MIL-49	Sheet	Buna-N	Military	50A	1/16"	36"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG507
BULK-RS-H50MIL-24	Sheet	Buna-N	Military	50A	3/32"	12"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50
BULK-RS-H50MIL-34	Sheet	Buna-N	Military	50A	3/32"	12"	36"	Black	Plain	Smooth	MIL-R-3065E, M5BG507
BULK-RS-H50MIL-39	Sheet	Buna-N	Military	50A	3/32"	36"	36"	Black	Plain	Smooth	MIL-G-1149 Type 1 Class 5 Grade 50