


Antistatic Acetal Plastic

Antistatic filler prevents the buildup of static charges and protects sensitive equipment from damage.



| Part Number | Shape | Material | Grade | Thickness | Width | Length | Color | Clarity | Backing Type | Specs Met |
|--------------|-------|----------|------------|-----------|-------|--------|-----------|---------|--------------|-----------|
| PS-AC-ESD-16 | Bar | Acetal | Antistatic | 1/4" | 1/2" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-37 | Bar | Acetal | Antistatic | 3/8" | 1/2" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-58 | Bar | Acetal | Antistatic | 1/2" | 1/2" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-17 | Bar | Acetal | Antistatic | 1/4" | 1/2" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-38 | Bar | Acetal | Antistatic | 3/8" | 1/2" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-59 | Bar | Acetal | Antistatic | 1/2" | 1/2" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-18 | Bar | Acetal | Antistatic | 1/4" | 1/2" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-39 | Bar | Acetal | Antistatic | 3/8" | 1/2" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-60 | Bar | Acetal | Antistatic | 1/2" | 1/2" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-22 | Bar | Acetal | Antistatic | 1/4" | 1" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-43 | Bar | Acetal | Antistatic | 3/8" | 1" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-64 | Bar | Acetal | Antistatic | 1/2" | 1" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-23 | Bar | Acetal | Antistatic | 1/4" | 1" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-44 | Bar | Acetal | Antistatic | 3/8" | 1" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-65 | Bar | Acetal | Antistatic | 1/2" | 1" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-24 | Bar | Acetal | Antistatic | 1/4" | 1" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-45 | Bar | Acetal | Antistatic | 3/8" | 1" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-66 | Bar | Acetal | Antistatic | 1/2" | 1" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-28 | Bar | Acetal | Antistatic | 1/4" | 2" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-49 | Bar | Acetal | Antistatic | 3/8" | 2" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-70 | Bar | Acetal | Antistatic | 1/2" | 2" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-29 | Bar | Acetal | Antistatic | 1/4" | 2" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-50 | Bar | Acetal | Antistatic | 3/8" | 2" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-71 | Bar | Acetal | Antistatic | 1/2" | 2" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-30 | Bar | Acetal | Antistatic | 1/4" | 2" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-51 | Bar | Acetal | Antistatic | 3/8" | 2" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-72 | Bar | Acetal | Antistatic | 1/2" | 2" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-34 | Bar | Acetal | Antistatic | 1/4" | 4" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-55 | Bar | Acetal | Antistatic | 3/8" | 4" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-76 | Bar | Acetal | Antistatic | 1/2" | 4" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-35 | Bar | Acetal | Antistatic | 1/4" | 4" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-56 | Bar | Acetal | Antistatic | 3/8" | 4" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-77 | Bar | Acetal | Antistatic | 1/2" | 4" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-36 | Bar | Acetal | Antistatic | 1/4" | 4" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-57 | Bar | Acetal | Antistatic | 3/8" | 4" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-78 | Bar | Acetal | Antistatic | 1/2" | 4" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-4 | Sheet | Acetal | Antistatic | 1/4" | 6" | 6" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-8 | Sheet | Acetal | Antistatic | 3/8" | 6" | 6" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-12 | Sheet | Acetal | Antistatic | 1/2" | 6" | 6" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-5 | Sheet | Acetal | Antistatic | 1/4" | 12" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-9 | Sheet | Acetal | Antistatic | 3/8" | 12" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-13 | Sheet | Acetal | Antistatic | 1/2" | 12" | 12" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-6 | Sheet | Acetal | Antistatic | 1/4" | 12" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-10 | Sheet | Acetal | Antistatic | 3/8" | 12" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-14 | Sheet | Acetal | Antistatic | 1/2" | 12" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-7 | Sheet | Acetal | Antistatic | 1/4" | 24" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-11 | Sheet | Acetal | Antistatic | 3/8" | 24" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-15 | Sheet | Acetal | Antistatic | 1/2" | 24" | 24" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-1 | Sheet | Acetal | Antistatic | 1/4" | 24" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-2 | Sheet | Acetal | Antistatic | 3/8" | 24" | 48" | Off-White | Opaque | Plain | UL 94 HB |
| PS-AC-ESD-3 | Sheet | Acetal | Antistatic | 1/2" | 24" | 48" | Off-White | Opaque | Plain | UL 94 HB |