

**ZPEB 2.5-2**

**2.5 mm<sup>2</sup>**

Two connections



5.1 x 33.5 x 31  
/ 4  
**0.13...4**



IEC 60947-7-2 Ex eb II C Gb **Ex** II 2 G D

IEC	UL	CSA	EN 60079-7
2.5	AWG 26...12	AWG 26...12	4 mm <sup>2</sup>
800			
8			
	300 A (2.5 mm <sup>2</sup> )		
	3		
	A2 / V-0		

CE CE UK IEC

**Rated connection**

0.5...4  
0.5...2.5 / 0.5...1.5

10 / 0.6 x 3.5 mm

TS 15 - block construction


Type	Qty.	Order No.
ZPEB 2.5-2	100	1712810000

Type	Qty.	Order No.
ZAP ZDUB	50	1704750000
ZEW 15	20	7920340000
SDIS SLIM 0.6X3.5X100	1	2749610000
DEK 5/5 MC NE WS	1000	1609801044
WS 10/5 MC NE WS	720	1635000000
DEK 5/5 MM WS	800	2007110000


**ZPE 1.5**

**1.5 mm<sup>2</sup>**

Two connections



3.5 x 54.5 x 36.5  
/ 1.5  
**0.05...1.5**



IEC 60947-7-2 Ex eb II C Gb **Ex** II 2 G D

IEC	UL	CSA	EN 60079-7
1.5	AWG 26...14	AWG 26...14	1.5 mm <sup>2</sup>
500			
6			
	180 A (1.5 mm <sup>2</sup> )		
	3		
	B1 / V-0		

CE CE UK IEC

**Rated connection**

0.5...1.5  
0.5...1.5 / 0.5...1.5  
0.5...0.75  
10 / 0.4 x 2.0 mm


Type	Qty.	Order No.
ZPE 1.5	50	1775510000

Type	Qty.	Order No.
ZAP/TW ZDU1.5/2AN	20	1776030000
ZEW 35	20	9540000000
SDS 0.4X2.0X60	1	2749260000
ZRH 1.5S/1	500	1781950000
DEK 5/3.5 MC NE WS	500	1755270000
WS 12/3.5 MC NE WS	600	1778270000
DEK 5/3.5 MM WS	1000	2007100000


**ZPE 1.5/3AN**

**1.5 mm<sup>2</sup>**

Three connections



3.5 x 63 x 36.5  
/ 1.5  
**0.05...1.5**



IEC 60947-7-2 Ex eb II C Gb **Ex** II 2 G D

IEC	UL	CSA	EN 60079-7
1.5	AWG 26...14	AWG 26...14	1.5 mm <sup>2</sup>
500			
6			
	180 A (1.5 mm <sup>2</sup> )		
	3		
	B1 / V-0		

CE CE UK IEC

**Rated connection**

0.5...1.5  
0.5...1.5 / 0.5...1.5  
0.5...0.75  
10 / 0.4 x 2.0 mm

Type	Qty.	Order No.
ZPE 1.5/3AN	50	1775560000

Type	Qty.	Order No.
ZAP/TW ZDU1.5/3AN	20	1776060000
ZEW 35	20	9540000000
SDS 0.4X2.0X60	1	2749260000
ZRH 1.5S/1	500	1781950000
DEK 5/3.5 MC NE WS	500	1755270000
WS 12/3.5 MC NE WS	600	1778270000
DEK 5/3.5 MM WS	1000	2007100000

