

ZPE 2.5-2/4AN

2.5 mm<sup>2</sup>

Four connections



5.1 x 50.5 x 43.5  
/ 4  
0.13...4



IEC 60947-7-2 Ex eb II C Gb II 2 G D

IEC	UL	CSA	EN 60079-7
2.5	AWG 26...12	AWG 26...14	4 mm <sup>2</sup>
800			
8			
	300 A (2.5 mm <sup>2</sup> )		
	3		
	A2 / V-0		

Rated connection

0.5...4  
0.5...2.5 / 0.5...1.5

10 / 0.6 x 3.5 mm

Type	Qty.	Order No.
ZPE 2.5-2/4AN	50	1706100000

Type	Qty.	Order No.
ZAP/TW7	50	1706110000
ZEW 35	20	9540000000
ZTA 4	11 A 25	1688110000
SDIS SLIM 0.6X3.5X100	1	2749610000
ZRH 1.5H/1	1000	1678810000
ZRH 1.5H/2	1000	1678800000
DEK 5/5 MC NE WS	1000	1609801044
WS 10/5 MC NE WS	720	1635000000
DEK 5/5 MM WS	800	2007110000

ZPE 4-2/2AN

4 mm<sup>2</sup>

Two connections



6.1 x 61.5 x 45.5  
/ 6  
0.13...6



IEC 60947-7-2 Ex eb II C Gb II 2 G D

IEC	UL	CSA	EN 60079-7
4	AWG 26...10	AWG 26...10	6 mm <sup>2</sup>
800			
8			
	480 A (4 mm <sup>2</sup> )		
	3		
	A3 / V-0		

Rated connection

0.5...6  
0.5...4 / 0.5...4

10 / 0.6 x 3.5 mm

Type	Qty.	Order No.
ZPE 4-2/2AN	50	1770380000

Type	Qty.	Order No.
ZAP ZDU4-2	50	1770400000
ZEW 35	20	9540000000
ZTA 6/ZA	17.5 A 25	1780660000
SDIS SLIM 0.6X3.5X100	1	2749610000
ZRH 4/1 WS	1000	1636640000
DEK 5/6 MC NE WS	1000	1609820000
WS 12/6 MC NE WS	600	1609900000
DEK 5/6 MM WS	600	2007120000

ZPE 4-2/3AN

4 mm<sup>2</sup>

Three connections



6.1 x 61.5 x 45.5  
/ 6  
0.13...6



IEC 60947-7-2 Ex eb II C Gb II 2 G D

IEC	UL	CSA	EN 60079-7
4	AWG 26...10	AWG 26...10	6 mm <sup>2</sup>
800			
8			
	480 A (4 mm <sup>2</sup> )		
	3		
	A3 / V-0		

Rated connection

0.5...6  
0.5...4 / 0.5...4

10 / 0.6 x 3.5 mm

Type	Qty.	Order No.
ZPE 4-2/3AN	50	1770390000

Type	Qty.	Order No.
ZAP ZDU4-2	50	1770400000
ZEW 35	20	9540000000
ZTA 6/ZA	17.5 A 25	1780660000
SDIS SLIM 0.6X3.5X100	1	2749610000
ZRH 4/1 WS	1000	1636640000
DEK 5/6 MC NE WS	1000	1609820000
WS 12/6 MC NE WS	600	1609900000
DEK 5/6 MM WS	600	2007120000

