



Anti-vibration U-band



Anti-vibration U-band with plate



A10616 Anti-vibration U-band

Confirm delivery

A12090 Anti-vibration U-band with plate

Confirm delivery

Anti-vibration supplementary U-band for SGP pipe / With 10 mm rubber

Part number A10616 Anti-vibration U-band

A12090 Anti-vibration U-band with plate

Units (mm)

Size code		Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	Screw diameter	t	C	P	H	L
A10616	A12090									
0026	0020	20A	3/4	27.2	W 3/8	2.3	25	61	44	30
0045	0034	25A	1	34.0	W 3/8	2.3	25	68	47	30
0050	0049	32A	1 1/4	42.7	W 3/8	2.3	25	77	52	30
0064	0053	40A	1 1/2	48.6	W 3/8	2.3	25	83	60	35
0079	0068	50A	2	60.5	W 3/8	2.3	25	95	66	35
0083	0072	65A	2 1/2	76.3	W 3/8	2.6	25	111	80	35
0098	0087	80A	3	89.1	W 3/8	2.6	25	124	85	35
0115	0091	100A	4	114.3	W 3/8	2.6	25	149	102	35
0120	0104	125A	5	139.8	W 1/2	4.5	32	181	130	60
0134	0119	150A	6	165.2	W 1/2	4.5	32	207	145	60

The shape of the rubber may change for larger diameters.

A10631 Stainless steel anti-vibration U-band

Made to order

A13153 Anti-vibration stainless steel U-band (with new-type rubber plate)

Made to order

Anti-vibration supplementary U-band for SGP pipe / With 10 mm rubber

Part number A10631 Stainless steel anti-vibration U-band


A13153 Anti-vibration U-band (with new-type rubber plate)

Units (mm)

Size code		Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	Screw diameter	t	C	P	H	L
A10631	A13153									
0022	0026	20A	3/4	27.2	W 3/8	2.0	25	61	54	50
0037	0045	25A	1	34.0	W 3/8	2.0	25	68	57	50
0041	0050	32A	1 1/4	42.7	W 3/8	2.0	25	77	61	50
0056	0064	40A	1 1/2	48.6	W 3/8	2.0	25	83	64	50
0075	0079	50A	2	60.5	W 3/8	2.0	25	96	70	50
0080	0083	65A	2 1/2	76.3	W 3/8	2.0	25	111	78	60
0094	0098	80A	3	89.1	W 3/8	2.0	25	124	85	65
0107	0115	100A	4	114.3	W 3/8	2.0	25	149	97	65
0111	0120	125A	5	139.8	W 1/2	3.0	32	181	119	80
0126	0134	150A	6	165.2	W 1/2	3.0	32	207	132	80

The shape of the rubber may change for larger diameters.

Stainless steel anti-vibration U-band



Anti-vibration stainless steel U-band with plate

