



TYPE		GLOBE			GLOBE			GLOBE			GLOBE			GLOBE			
Ductile Iron																	
FIG		16SP			16SPB			16SPBO			20SY			20SYB			
PRESSURE		16K			16K			16K			20K			20K			
END CONNECTION		BS21 (JIS B0203)			JIS B2239			JIS B2239			BS21 (JIS B0203)			JIS B2239			
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	3/8	10	64	110	60	108	111	60	—	—	—	75	136	70	110	136	70
	1/2	15	70	122	80	108	122	80	—	—	—	78	138	80	110	138	80
	3/4	20	85	128	80	117	128	80	—	—	—	91	157	100	120	157	100
	1	25	95	147	100	127	146	100	—	—	—	105	178	115	130	178	115
	1 1/4	32	110	165	115	140	165	115	—	—	—	122	202	135	160	202	135
	1 1/2	40	125	182	115	165	182	115	—	—	—	135	210	135	180	210	135
	2	50	145	196	135	203	198	135	203	302	200	160	239	180	230	239	180
	2 1/2	65	—	—	—	—	—	—	216	313	225	—	—	—	—	—	—
	3	80	—	—	—	—	—	—	241	356	250	—	—	—	—	—	—
	4	100	—	—	—	—	—	—	292	377	250	—	—	—	—	—	—
	5	125	—	—	—	—	—	—	356	460	300	—	—	—	—	—	—
	6	150	—	—	—	—	—	—	406	524	350	—	—	—	—	—	—
	8	200	—	—	—	—	—	—	495	585	400	—	—	—	—	—	—
BODY		Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
BONNET		Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
STEM		Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			Stainless Steel			
DISC		Stainless Steel			Stainless Steel			Stainless Steel / Ductile Iron			Stainless Steel+HF			Stainless Steel+HF			

TYPE		GLOBE			GLOBE			LIFT CHECK			LIFT CHECK			LIFT CHECK			
Ductile Iron																	
FIG		150SPB			150SPDB			10SF			10SFBF			10SN			
PRESSURE		Class 150			Class 150			10K			10K			10K			
END CONNECTION		ASME B16.5			ASME B16.5			BS21 (JIS B0203)			JIS B2239			BS21 (JIS B0203)			
DIMENSIONS	inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D
	1/2	15	108	122	80	108	127	70	65	39	—	85	39	—	70	50	—
	3/4	20	117	128	80	117	135	70	80	42	—	95	42	—	80	53	—
	1	25	127	146	100	127	155	90	90	48	—	110	48	—	90	61	—
	1 1/4	32	140	165	115	140	172	100	105	56	—	130	56	—	110	69	—
	1 1/2	40	165	179	115	165	193	115	120	65	—	150	65	—	120	75	—
	2	50	203	198	135	203	208	135	140	73	—	180	73	—	140	87	—
BODY		Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			Ductile Iron			
BONNET		Ductile Iron			Ductile Iron			—			—			—			
CAP		—			—			Stainless Steel			Stainless Steel			Stainless Steel			
STEM		Stainless Steel			Stainless Steel			—			—			—			
DISC		Stainless Steel			G/F PTFE			Stainless Steel			Stainless Steel			Stainless Steel			
					Soft Seated disc												