

Shock Absorbing Castors V NEW

—Torsion spring type
(Steel/Stainless steel)—

Traveling speed up to 4km/h

RoHS compliant products.

Patent No. 4579285

POINT

- **Unique design; Shock absorbing spring integrated with the main frame of the castor.**
- Torsion spring type **absorbs shock and vibration from every direction and reduces noise in operation.**
- 2 types of brackets are available according to wire diameter; TS4 (wire diameter 4mm): Spring load is 10kg. Load capacity is 20kg. TS6 (wire diameter 6mm): Spring load is 50kg. Load capacity is 70kg.
- Thanks to absorbing function, **impact loading to swivel head and wheel bearings can be lowered, leading to an increased service life of the product.**
- For TS4, **special cover** is available for safe handling, and dust prevention; comes in green, orange, blue, smoke grey made of EVA, and grey made of TPE.

USE EXAMPLE

- For medical equipment and catering carts.
 - For light duty carriers.
 - For various design carts.
- ◎We'll accept your custom-order. Please feel free to contact us.
(Use "Specification Form for Custom-designed castor" at the end of this catalog.)
- ◎Please feel free to ask about the product weight for each item.

SAJ-TS4 Swivel castors Steel

SAJ-TS4-50
SAJ-TS4-75
SAJ-TS4-100

• Color/Finish; Zinc plated with CrⅢ, Zinc plated with CrⅢ (Black)

SUSAJ-TS4 Swivel castors Stainless steel

SUSAJ-TS4-50
SUSAJ-TS4-75
SUSAJ-TS4-100

SAJ-TS4-SJ Threaded stem fitting Steel

SAJ-TS4-SJ-50
SAJ-TS4-SJ-75
SAJ-TS4-SJ-100

• Color/Finish; Zinc plated with CrⅢ, Zinc plated with CrⅢ (Black)

SUSAJ-TS4-SJ Threaded stem fitting Stainless steel

SUSAJ-TS4-SJ-50
SUSAJ-TS4-SJ-75
SUSAJ-TS4-SJ-100

SAJ-TS4-SC Stem fitting Steel

SAJ-TS4-SC-50
SAJ-TS4-SC-75
SAJ-TS4-SC-100

• Color/Finish; Zinc plated with CrⅢ, Zinc plated with CrⅢ (Black)

SUSAJ-TS4-SC Stem fitting Stainless steel

SUSAJ-TS4-SC-50
SUSAJ-TS4-SC-75
SUSAJ-TS4-SC-100

SAJ-TS6 Swivel castors Steel

SAJ-TS6-50
SAJ-TS6-75
SAJ-TS6-100

• Color/Finish; Zinc plated with CrⅢ

SUSAJ-TS6 Swivel castors Stainless steel

SUSAJ-TS6-50
SUSAJ-TS6-75
SUSAJ-TS6-100

SAJ-TS6-SJ Threaded stem fitting Steel

SAJ-TS6-SJ-50
SAJ-TS6-SJ-75
SAJ-TS6-SJ-100

• Color/Finish; Zinc plated with CrⅢ

SUSAJ-TS6-SJ Threaded stem fitting Stainless steel

SUSAJ-TS6-SJ-50
SUSAJ-TS6-SJ-75
SUSAJ-TS6-SJ-100

SAJ-TS6-SC Stem fitting Steel

SAJ-TS6-SC-50
SAJ-TS6-SC-75
SAJ-TS6-SC-100

• Color/Finish; Zinc plated with CrⅢ

SUSAJ-TS6-SC Stem fitting Stainless steel

SUSAJ-TS6-SC-50
SUSAJ-TS6-SC-75
SUSAJ-TS6-SC-100

 ...Steel  ...Stainless steel