

STRAIGHT GUIDE POSTS FOR BALL BEARING APPLICATIONS

LEMPCO Straight Guide Posts for ball bearing assemblies are manufactured from 52100 tool steel and precision ground. See pages 13–15 for mounting instructions.

Post Diameter A	Length L	Catalog Number
3/4 (.753)	3	951-0612
	3 1/4	951-0613
	3 1/2	951-0614
	3 3/4	951-0615
	4	951-0616
	4 1/4	951-0617
	4 1/2	951-0618
	4 3/4	951-0619
	5	951-0620
	5 1/2	951-0622
6	951-0624	
1 (1.003)	3 3/4	951-0815
	4	951-0816
	4 1/4	951-0817
	4 1/2	951-0818
	4 3/4	951-0819
	5	951-0820
	5 1/4	951-0821
	5 1/2	951-0822
	5 3/4	951-0823
	6	951-0824
	6 1/2	951-0826
	7	951-0828
	7 1/2	951-0830
	8	951-0832
8 1/2	951-0834	
9	951-0836	
10	951-0840	
11	951-0844	
12	951-0848	
1 1/4 (1.253)	4 1/2	951-1018
	4 3/4	951-1019
	5	951-1020
	5 1/4	951-1021
	5 1/2	951-1022
	5 3/4	951-1023
	6	951-1024
	6 1/2	951-1026
	7	951-1028
	7 1/2	951-1030
	8	951-1032
	8 1/2	951-1034
	9	951-1036
	10	951-1040
11	951-1044	
12	951-1048	

Post Diameter A	Length L	Catalog Number
1 1/2 (1.503)	4 1/2	951-1218
	4 3/4	951-1219
	5	951-1220
	5 1/4	951-1221
	5 1/2	951-1222
	5 3/4	951-1223
	6	951-1224
	6 1/2	951-1226
	7	951-1228
	7 1/2	951-1230
	8	951-1232
	8 1/2	951-1234
	9	951-1236
	9 1/2	951-1238
10	951-1240	
10 1/2	951-1242	
11	951-1244	
11 1/2	951-1246	
12	951-1248	
12 1/2	951-1250	
13	951-1252	
14	951-1256	
1 3/4 (1.753)	5	951-1420
	5 1/4	951-1421
	5 1/2	951-1422
	5 3/4	951-1423
	6	951-1424
	6 1/4	951-1425
	6 1/2	951-1426
	7	951-1428
	7 1/2	951-1430
	8	951-1432
	8 1/2	951-1434
	9	951-1436
	9 1/2	951-1438
	10	951-1440
10 1/2	951-1442	
11	951-1444	
11 1/2	951-1446	
12	951-1448	
12 1/2	951-1450	
13	951-1452	
14	951-1456	
15	951-1460	
17	951-1468	

Post Diameter A	Length L	Catalog Number
2 (2.003)	5 1/2	951-1622
	5 3/4	951-1623
	6	951-1624
	6 1/4	951-1625
	6 1/2	951-1626
	6 3/4	951-1627
	7	951-1628
	7 1/4	951-1629
	7 1/2	951-1630
	7 3/4	951-1631
	8	951-1632
	8 1/2	951-1634
	9	951-1636
	9 1/2	951-1638
	10	951-1640
	10 1/2	951-1642
	11	951-1644
	11 1/2	951-1646
12	951-1648	
12 1/2	951-1650	
13	951-1652	
14	951-1656	
15	951-1660	
16	951-1664	
17	951-1668	
18	951-1672	
2 1/2 (2.503)	8	951-2032
	8 1/2	951-2034
	9	951-2036
	10	951-2040
	11	951-2044
	12	951-2048
	13	951-2052
	14	951-2056
17	951-2068	
20	951-2080	
3 (3.003)	8	951-2432
	8 1/2	951-2434
	9	951-2436
	10	951-2440
	11	951-2444
	12	951-2448
	13	951-2452
	14	951-2456
17	951-2468	
20	951-2480	

