



**FA-810**  
鉄製

# コンテナハンドル

## CONTAINER HANDLES

ハンドル・取手  
つまみ・周辺機器



A

クレモン

ローラー  
締め

SPECIALY-EQUIPPED HANDLES

- 特装密閉ハンドル
- フリーザー密閉
- 平面スイング
- ギア式
- 平面ハンドル
- ポップハンドル
- リフトハンドル
- アジャストハンドル
- ラッチ式
- スナッチ
- リンク
- フック式
- ロックハンドル
- L型ハンドル
- T型ハンドル
- 丸型小型
- 押ボタン
- 取手
- つまみ
- 止め金  
ロッド棒
- ジョイント  
リンク
- ワイヤ

### 特徴 Feature

- 左右兼用型
- For both left-hand and right-hand use.

- 仕様 ●材質： 鋳鉄(FCD400)  
●表面仕上： 亜鉛めっきクロメート処理(MFZn-C)
- 用途 ●コンテナ車・冷凍冷蔵車・保冷車専用
- 納期 ●標準在庫品
- 備考 ●ハンドルとパイプは組立していません。パイプは別売です。
- ⚠ ●軸受けはポリエチレン製(PE)のため常温でご使用下さい。高温環境下でのご使用はお問合せ下さい。
- パイプ径φ34用も製作致します。お問合せ下さい。

- Specifications ●Material: Ferrum casting iron (FCD400)  
●Finish: Zinc plating chromate treatment (MFZn-C)
- Specific use ●Containers, chill and cold storage vehicles
- Remarks ●The handle and the pipe are not assembled. The pipe is optional.
- ⚠ ●The bearing is made of polyethylene (PE) and should be used at ordinary temperature. Please contact Takigen if it will be used in a high-temperature environment.



**FA-810-C-2**



**FA-810-C-4**

ワンタッチのハンドル受けがございます。  
One-touch lock handle catches is also available.

詳細は167~176ページをご参照下さい。  
See pages 167~176 for detail.

FA-810-1



商品番号 Product No.	RoHS	CAD	製品質量(g) Mass	コード Code	単価 Price	量販価格 数量 Quantity	Bulk Price 単価 Price
FA-810-1	●	2D/3D	4,570	60078	¥8,100	5個~	¥7,776
FA-810-2	●	2D/3D	2,900	60079	¥4,600	5個~	¥4,416
FA-810-3	●	2D/3D	1,900	60080	¥4,200	5個~	¥4,032

商品番号 Product No.	適用パイプ径 Applicable pipe diameter	(L1)	L2	(L3)	L4	(L5)	L6	(L7)	(W1)	W2	W3	(W4)	(H1)	(H2)	(H3)	H5	(H6)	P1	P2	P3	P4	φD	φd	t
FA-810-1	φ27.2(t=3)	49	341	160~220	152	82	22.5	26	133	37	14	31.5	54	12	10	32	56	96.5	114	27.2	9	2.3		
FA-810-2	φ27.2(t=3)	53	246	125~155	16	33	82	18	21	92	37	11.5	31.5	51	13	7	32	34	56	71.5	77	27.2	8	2.3
FA-810-3	φ21.7(t=3)	38	207	120	16	33	77	16	19	105	35	8.5	24	37.5	8	7	23	44.5	49	68.5	77	21.7	8	2

●: RoHS指令対応品

▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。

