

# マルチ取手

## PULLS



### 特徴 Feature

- ファッションブルな扉にマッチしたハンドルです。
- 取付けは表(M4ねじ)・裏(M4タッピンねじ)両面から使用できます。
- Match with fashionable doors.
- Can be installed on both the front (M4 screw) and rear (M4 tapping) sides.

**仕様** ●材 質：パイプ/硬質ポリ塩化ビニル(PVC)ブラケット/ポリアミドMXD6  
●標準色：パイプ/オレンジ・イエロー  
ブラケット/ブラウン

**用途** ●各種キャビネット・通信機器  
**納期** ●標準在庫品  
**備考** ●適用板厚以外でご使用の際は別途ねじをご用意下さい。  
●表付け用M4皿ねじは添付されておりません。  
●表付けでご使用する場合は、座部を45°回転させ、穴と穴の間にねじを通すようにして取付け下さい。

**Specifications** ●Material: Pipe: Hard polyvinyl chloride(PVC) Bracket: Polyamide MXD6  
●Standard color: Pipe/Orange, yellow. Bracket/Brown

**Specific-use** ●Communication appliances, various kinds of cabinets.  
**Remarks** ●Prepare other types of screws for other panel thickness than the applicable panel thickness.  
●M4 flat countersunk head screws for front attachment are not attached.  
●For front attachment of the handle, rotate its fitting roots by 45° to insert the screws through the openings between the screw holes for rear attachment.



AP-194-1-Orange  
オレンジ









AP-194-3-Yellow  
イエロー



AP-194-T

AP-194-J



商品番号 Product No.	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price 数量 Quantity 単価 Price
AP-194-J	33	01149	¥230	30個~ ¥221
AP-194-T	55	01148	¥290	30個~ ¥278

商品番号 Product No.	適用板厚(裏付け) Applicable panel thickness (Rear installation)	製品質量(g) Mass	コード Code	単価 Price	量販価格 Bulk Price 数量 Quantity 単価 Price
AP-194-1-Orange オレンジ	5~20	190	01073	¥900	12個~ ¥864
AP-194-1-Yellow イエロー	5~20	190	01074	¥900	12個~ ¥864
AP-194-2-Orange オレンジ	10~20	160	01075	¥850	12個~ ¥816
AP-194-2-Yellow イエロー	10~20	160	01076	¥850	12個~ ¥816
AP-194-3-Orange オレンジ	20	115	01077	¥800	20個~ ¥768
AP-194-3-Yellow イエロー	20	115	01078	¥800	20個~ ¥768

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。 ※大量のご注文は更にお安くなります。

- クレモン
- ローラー  
締り
- 特装密閉  
ハンドル
- フリーザー  
密閉
- 平面  
スイング
- ギア式
- 平面  
ハンドル
- ポップ  
ハンドル
- リフト  
ハンドル
- アジャスト  
ハンドル
- ラッチ式
- スナッチ
- リンク
- フック式
- ロック  
ハンドル
- L型  
ハンドル
- T型  
ハンドル
- 丸型  
小型
- 押ボタン
- 取手  
PULLS
- つまみ
- 止め金  
ロッド棒
- ジョイント  
リンク
- ワイヤ