



注記
NOTES

- 適合/ワシニング アッセンブリ; 52213-*** | APPLICABLE HS'G ASS'Y; 52213-***
- 嵌合相手; 50147-8*00
MATES WITH; 50147-8*00

50148-8100	バラ状 LOOSE
50148-8000	連鎖状 CHAIN
MATERIAL NO.	端子形状 FORM

molex

2.5 MINI WATERPROOF
CRIMP REC

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER: SD-50148-001 PSD 001 B2

SEE CHART GENERAL MARKET 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
DEVISION UNITS: mm	SCALE: 10:1
GENERAL TOLERANCES UNLESS SPECIFIED:	CURRENT REV DESC:
AMOUNT TOL. 1 0.1	EC NO: 629483
2 PLACES 0.2	DRWN: MSATO08 2019/12/18
3 PLACES 0.25	CHKD: HIJIMA 2019/12/20
4 PLACES 0.3	APPR: TOSADA 2019/12/20
1 PLACE 0.3	INITIAL REVISION:
2 PLACES 0.3	DRWN: SINACBA 2012/02/03
1 PLACE 0.3	APPR: MAYAMAMOTO 2019/02/03
DRAFT BRIDGE APPLICABLE MOST FREQUENT WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
	DRAWING SERIES: A3-SIZE 50148

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER	±0.2	
10 OVER 30 UNDER	±0.25	
30 OVER	±0.3	
ANGULAR ±3°		

INITIAL REVISION:		
DRWN M.SANO	1991/07/17	
CHECK M.SAKANO	1992/08/06	
APPR M.ENOMOTO	1992/08/06	

材料 MATERIAL	リン青銅 錫メッキ (+0.2) PHOSPHOR BRONZE TIN PLATING (+0.2)
適用電線範囲 WIRE RANGE	AVSS-0.3/0.3F AVSS-0.5/0.5F CAVS-0.3 CAVS-0.5 ISO-0.5 AWG #22/#20
被覆外径 INS. RANGE	φ1.4-1.9
DOCUMENT STATUS	P1 RELEASE DATE 2019/12/20 08:34:22

10 9 8 7 6 5 4 3 2 1