



Stock 38,650 Items

"Neji-Saurus GT"



Tip Shape



TPZ-58

- Features**
- A rescue tool for "screw trouble".
 - Adopted the original color considering the design.
 - Attaching the cutting blade, it can cut copper wires of $\Phi 1.2\text{mm}$ easily.
 - Grasps the crushed screws, rusted screws, fastening screws and removes them.
- Specs**
- With mechanical spring
 - **Compatible Truss/Pan Head Screw/Tip Holding Part:** $\Phi 3$ to $\Phi 9.5$, **Main Body Holding Part:** $\Phi 5.5$ to $\Phi 10$
- Origin**
- Japan

Strong jaw that can cut electric wires



Low Head Truss Screw Sharp teeth that also grips on to



Further Evolved Latitudinal Groove



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Grip Width (mm)	Tip Width (mm)	Thickness (mm)	Tip Length (mm)	SPQ (piece)	Weight (g)
437-8229	TPZ-58	¥2,592	¥2,800	160	54	17.5	8.5	28	5	130

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock 641 Items

"Neji-Saurus Z(zeta)"




Tip Shape



PZ-60

- Features**
- Equipped with "gear teeth" that can reliably hold even thin objects such as shim plate.
 - Can cut thin wire with lighter force compared to any normal needle-nose pliers.
 - The cross section of the grip is a T shape and it is lightweight and prevents twisting of the grip.
 - Essential tool for field maintenance.
 - Needle-nose pliers type product that can remove screws even in narrow and recessed places.
- Specs**
- Cutting performance: Copper wire $\Phi 1.2\text{mm}$
 - **Adaptable screw size: Screw head diameter of $\Phi 2$ to 5.5mm , screw head height of up to 2.2mm**
- Origin**
- Japan

Vertical grooves to remove screws



Gear teeth that can hold even thin plates



Can also cut extra fine wire



Lightweight & resistant-to-twist T-shaped grip



Order Unit: 1 Piece

ENGINEER INC.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Grip Width (mm)	Tip Width (mm)	Thickness (mm)	Tip Length (mm)	SPQ (piece)	Weight (g)
819-9083	PZ-60	¥3,309	¥3,300	190	57.5	19.5	15	56	5	180

Contact us: 06-6974-0100 <http://www.engineer.jp/>



Stock 641 Items

"Neji-Saurus RX"



Tip Shape



PZ-59

- Features**
- By its own mechanism, it can even grasp very thin plates firmly.
 - Grasp the screw head that you can not turn with the screwdriver and remove it.
 - Attaching the cutting blade, it can cut objects easily.
- Specs**
- **Compatible Screw (truss/pan)/Holding Part at the Tip:** $\Phi 3$ to $\Phi 15$
- Origin**
- Japan



Gear teeth



T Type Grip

Order Unit: 1 Piece

(Price revision date: Jul, 2015) ENGINEER INC.

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Grip Width (mm)	Tip Width (mm)	Thickness (mm)	Tip Length (mm)	SPQ (piece)	Weight (g)
481-5033	PZ-59	¥3,690	¥3,680	204	53	27	14	27.7	5	300

Contact us: 06-6974-0100 <http://www.engineer.jp/>