


PEEK/LC

ポリエーテルエーテルケトン / 六角穴付低頭ボルト
Polyether ether ketone / Hexagon socket low head cap bolt




品番 Product number		PEEK/LC-M○-L○							
M	M3	M4	M5	M6					
ピッチ / Pitch	0.5	0.7	0.8	1					
D × H	5.5 × 2	7 × 2.8	8.5 × 3.5	10 × 4					
B	2	2.5	3	4					
L	6	100	100	100	—				
	8	100	100	100	—				
	10	100	100	100	100				
	12	100	100	100	100				
	16	100	100	100	100				
	20	100	100	100	100				
	25	—	100	100	100				
	30	—	—	100	100				
	40	—	—	—	100				

販売単位 Quantity

PEEK/LH

ポリエーテルエーテルケトン / ヘキサロビュラ穴付低頭ボルト
Polyether ether ketone / Hexalobular socket low head cap bolt




品番 Product number		PEEK/LH-M○-L○							
M	M3	M4	M5	M6					
ピッチ / Pitch	0.5	0.7	0.8	1					
D × H	5.5 × 2.4	7 × 3.1	8.5 × 3.65	10 × 4.4					
穴番号 / Hexalobular number	10	20	25	30					
L	6	100	100	100	—				
	8	100	100	100	—				
	10	100	100	100	100				
	12	100	100	100	100				
	16	100	100	100	100				
	20	100	100	100	100				
	25	—	100	100	100				
	30	—	—	100	100				
	40	—	—	—	100				

販売単位 Quantity

PEEK/SH

ポリエーテルエーテルケトン / ヘキサロビュラ穴付極低頭ボルト
Polyether ether ketone / Hexalobular socket special low head cap bolt



品番 Product number		PEEK/SH-M○-L○							
M	M3	M4	M5	M6					
ピッチ / Pitch	0.5	0.7	0.8	1					
D × H	6 × 1.3	8 × 1.5	9 × 1.5	10 × 1.5					
穴番号 / Hexalobular number	8	10	15	20					
L	6	100	100	100	—				
	8	100	100	100	—				
	10	100	100	100	100				
	12	100	100	100	100				
	16	100	100	100	100				
	20	100	100	100	100				
	25	—	100	100	100				
	30	—	—	100	100				
	40	—	—	—	100				

販売単位 Quantity

ORDER ▶ 品番・サイズ・販売単位にてご注文ください **RoHS compliant**

- NEW
- PC
- PPS
- RENVY
- PEEK
- PVC
- PI
- PP
- PTFE
- PFA
- PVDF
- CERAMIC
- ワッシャー
- ローレット
- 特殊ボルト
- スペーサー
- リベット
- ワッシュ
- 結束バンド
- フラばね
- オゾン