











Type	Butterfly				Butterfly				Butterfly			Butterfly			Butterfly			
																		
Fig	PN10ALZ-N-LUE<Z0T01>				PN10ALZ-N-GUE<Z0T01>				10ALM-N-LU<Z0T01>			10ALM-N-LUE<Z0T01>			10ALM-N-GU<Z0T01>			
Product Code	552-UEL				552-UEG				550LA			550LA			550GA			
inch	mm	L	H	D	L	H	D	B	L	H	D	L	H	D	L	H	D	B
11/2	40								33	163	188	33	163	188	33	177	100	131
2	50	43	170	188	43	180	100	131	43	167	188	43	167	188	43	181	100	131
2 1/2	65	46	178	188	46	188	100	131	46	175	188	46	175	188	46	189	100	131
3	80	46	188	188	46	198	100	131	46	185	188	46	185	188	46	199	100	131
4	100	52	198	188	52	208	100	131	52	195	188	52	195	188	52	209	100	131
5	125	56	242	260	56	255	100	132	56	239	260	56	239	260	56	255	100	132
6	150	56	254	260	56	267	100	132	56	251	260	56	251	260	56	267	100	132
8	200	60	282	350	60	303	140	149							60	303	140	149
Body	Aluminum Die-cast				Aluminum Die-cast				Aluminum Die-cast			Aluminum Die-cast			Aluminum Die-cast			
Stem	Stainless Steel				Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel			
Disc	Stainless Steel				Stainless Steel				Stainless Steel			Stainless Steel			Stainless Steel			
Seat Rubber	EPDM				EPDM				NBR			EPDM			NBR			
Note																		

Type	Butterfly				Butterfly				Butterfly			Butterfly				Butterfly			
																			
Fig	10ALM-N-GUE<Z0T01>				10ALM-N-GE<Z0T01>				200L1-N<Z0T06>			200L2-N<Z0T06>				200L1-N-B<Z0T06>			
Product Code	550GA				550GA				917-DNSL			917-DNSG				917-BNSL			
inch	mm	L	H	D	B	L	H	D	B	L	H	D	L	H	D	B	L	H	D
11/2	40	33	177	100	131														
2	50	43	181	100	131					42.9	191	180	42.9	194	80	122	42.9	191	180
2 1/2	65	46	189	100	131					46	199	180	46	202	80	122	46	199	180
3	80	46	199	100	131					46	217	180	46	236	110	135	46	217	180
4	100	52	209	100	131					52.3	227	180	52.3	246	110	135	52.3	227	180
5	125	56	255	100	132					55.6	265	230	55.6	274	110	150	55.6	265	230
6	150	56	267	100	132					55.6	277	230	55.6	286	110	150	55.6	277	230
8	200	60	303	140	149					60.5	295	350	60.5	325	170	180	60.5	295	350
10	250	68	405	170	180	68	405	170	180										
12	300	78	430	170	180	78	430	170	180										
Body	Aluminum Die-cast				Aluminum Die-cast				Ductile Iron			Ductile Iron				Ductile Iron			
Stem	Stainless Steel				Stainless Steel				Stainless Steel			Stainless Steel				Stainless Steel			
Disc	Stainless Steel				Stainless Steel				Ductile Iron			Ductile Iron				Aluminum Bronze			
O ring	EPDM				EPDM														
Seat Rubber	EPDM				EPDM				NBR			NBR				NBR			
Note																			