


# Oil Resistant Buna-N Foam

## Buna-N Foam

Buna-N displays excellent strength and is the standard choice when oil resistance is required. This material also resists water and mild chemicals. Commonly found in applications related to automotive, engines, fuel systems, marine, and oil and gas.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture	Specs Met
ZUSABSR-67	Strip	Closed Cell	Buna-N	Standard	1/16"	1/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-1	Strip	Closed Cell	Buna-N	Standard	1/16"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-6	Strip	Closed Cell	Buna-N	Standard	1/16"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-13	Strip	Closed Cell	Buna-N	Standard	1/16"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-22	Strip	Closed Cell	Buna-N	Standard	1/16"	5/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-32	Strip	Closed Cell	Buna-N	Standard	1/16"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-43	Strip	Closed Cell	Buna-N	Standard	1/16"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-55	Strip	Closed Cell	Buna-N	Standard	1/16"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-68	Strip	Closed Cell	Buna-N	Standard	3/32"	1/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-2	Strip	Closed Cell	Buna-N	Standard	3/32"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-7	Strip	Closed Cell	Buna-N	Standard	3/32"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-14	Strip	Closed Cell	Buna-N	Standard	3/32"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-23	Strip	Closed Cell	Buna-N	Standard	3/32"	5/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-33	Strip	Closed Cell	Buna-N	Standard	3/32"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-44	Strip	Closed Cell	Buna-N	Standard	3/32"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-56	Strip	Closed Cell	Buna-N	Standard	3/32"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-69	Strip	Closed Cell	Buna-N	Standard	1/8"	1/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-3	Strip	Closed Cell	Buna-N	Standard	1/8"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-8	Strip	Closed Cell	Buna-N	Standard	1/8"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-15	Strip	Closed Cell	Buna-N	Standard	1/8"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-24	Strip	Closed Cell	Buna-N	Standard	1/8"	5/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-34	Strip	Closed Cell	Buna-N	Standard	1/8"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-45	Strip	Closed Cell	Buna-N	Standard	1/8"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-57	Strip	Closed Cell	Buna-N	Standard	1/8"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-4	Strip	Closed Cell	Buna-N	Standard	3/16"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-9	Strip	Closed Cell	Buna-N	Standard	3/16"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-16	Strip	Closed Cell	Buna-N	Standard	3/16"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-25	Strip	Closed Cell	Buna-N	Standard	3/16"	5/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-35	Strip	Closed Cell	Buna-N	Standard	3/16"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-46	Strip	Closed Cell	Buna-N	Standard	3/16"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-58	Strip	Closed Cell	Buna-N	Standard	3/16"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302
ZUSABSR-5	Strip	Closed Cell	Buna-N	Standard	1/4"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	ASTM D1056 2B2, FMVSS-302