


Low Compression Set Polyurethane Foam

Polyurethane foam is a versatile material used for shock absorption and cushioning. With its micro-cellular structure, this polyurethane withstands repetitive and extended periods of compression longer than other foam materials. It is an excellent shock absorbing material and is often used inside devices and equipment that need to last for several years, such as phones, cars, and helmets.



Part Number	Shape	Cell Type	Material	Grade	Thickness	Width	Length	Color	Firmness	Backing Type	Texture	Specs Met
ZUSA-MCP-1	Strip	Open Cell	Polyurethane	Low Compression Set	1/8"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-4	Strip	Open Cell	Polyurethane	Low Compression Set	1/8"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-2	Strip	Open Cell	Polyurethane	Low Compression Set	1/8"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-3	Strip	Open Cell	Polyurethane	Low Compression Set	1/8"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-5	Strip	Open Cell	Polyurethane	Low Compression Set	1/8"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-6	Strip	Open Cell	Polyurethane	Low Compression Set	1/8"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-7	Strip	Open Cell	Polyurethane	Low Compression Set	3/16"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-10	Strip	Open Cell	Polyurethane	Low Compression Set	3/16"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-8	Strip	Open Cell	Polyurethane	Low Compression Set	3/16"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-9	Strip	Open Cell	Polyurethane	Low Compression Set	3/16"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-11	Strip	Open Cell	Polyurethane	Low Compression Set	3/16"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-12	Strip	Open Cell	Polyurethane	Low Compression Set	3/16"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-13	Strip	Open Cell	Polyurethane	Low Compression Set	1/4"	1/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-16	Strip	Open Cell	Polyurethane	Low Compression Set	1/4"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-14	Strip	Open Cell	Polyurethane	Low Compression Set	1/4"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-15	Strip	Open Cell	Polyurethane	Low Compression Set	1/4"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-17	Strip	Open Cell	Polyurethane	Low Compression Set	1/4"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-18	Strip	Open Cell	Polyurethane	Low Compression Set	1/4"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-21	Strip	Open Cell	Polyurethane	Low Compression Set	3/8"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-19	Strip	Open Cell	Polyurethane	Low Compression Set	3/8"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-20	Strip	Open Cell	Polyurethane	Low Compression Set	3/8"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-22	Strip	Open Cell	Polyurethane	Low Compression Set	3/8"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-23	Strip	Open Cell	Polyurethane	Low Compression Set	3/8"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-26	Strip	Open Cell	Polyurethane	Low Compression Set	1/2"	3/8"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-24	Strip	Open Cell	Polyurethane	Low Compression Set	1/2"	1/2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-25	Strip	Open Cell	Polyurethane	Low Compression Set	1/2"	3/4"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-27	Strip	Open Cell	Polyurethane	Low Compression Set	1/2"	1"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-28	Strip	Open Cell	Polyurethane	Low Compression Set	1/2"	2"	10 ft.	Black	Soft (5 - 8 psi)	Acrylic Adhesive	Smooth	UL 94 HB
ZUSA-MCP-39	Sheet	Open Cell	Polyurethane	Low Compression Set	1/8"	1/2"	24"	Black	Soft (5 - 8 psi)	Plain	Smooth	UL 94 HB
ZUSA-MCP-34	Sheet	Open Cell	Polyurethane	Low Compression Set	1/8"	12"	12"	Black	Soft (5 - 8 psi)	Plain	Smooth	UL 94 HB
ZUSA-MCP-35	Sheet	Open Cell	Polyurethane	Low Compression Set	3/16"	12"	12"	Black	Soft (5 - 8 psi)	Plain	Smooth	UL 94 HB
ZUSA-MCP-40	Sheet	Open Cell	Polyurethane	Low Compression Set	3/16"	54"	24"	Black	Soft (5 - 8 psi)	Plain	Smooth	UL 94 HB