


Multipurpose Neoprene Rubber

Neoprene Rubber

Neoprene has a good balance of properties and is suitable for oils, water, and refrigerants while remaining tough and weather resistant.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-N30-93	Strip	Neoprene	Standard	30A	1/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-103	Strip	Neoprene	Standard	30A	1/32"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-113	Strip	Neoprene	Standard	30A	1/32"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-94	Strip	Neoprene	Standard	30A	1/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-104	Strip	Neoprene	Standard	30A	1/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-114	Strip	Neoprene	Standard	30A	1/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-95	Strip	Neoprene	Standard	30A	3/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-105	Strip	Neoprene	Standard	30A	3/32"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-115	Strip	Neoprene	Standard	30A	3/32"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-96	Strip	Neoprene	Standard	30A	1/8"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-106	Strip	Neoprene	Standard	30A	1/8"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-116	Strip	Neoprene	Standard	30A	1/8"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-97	Strip	Neoprene	Standard	30A	3/16"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-107	Strip	Neoprene	Standard	30A	3/16"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-117	Strip	Neoprene	Standard	30A	3/16"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-98	Strip	Neoprene	Standard	30A	1/4"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-108	Strip	Neoprene	Standard	30A	1/4"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-118	Strip	Neoprene	Standard	30A	1/4"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-99	Strip	Neoprene	Standard	30A	3/8"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-109	Strip	Neoprene	Standard	30A	3/8"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-100	Strip	Neoprene	Standard	30A	1/2"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-110	Strip	Neoprene	Standard	30A	1/2"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-119	Strip	Neoprene	Standard	30A	1/2"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-101	Strip	Neoprene	Standard	30A	3/4"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-111	Strip	Neoprene	Standard	30A	3/4"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-102	Strip	Neoprene	Standard	30A	1"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-112	Strip	Neoprene	Standard	30A	1"	4"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-120	Strip	Neoprene	Standard	30A	1"	6"	36"	Black	Plain	Smooth	ASTM D2000 BC 310
BULK-RS-N30-37	Strip	Neoprene	Standard	30A	1/32"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-47	Strip	Neoprene	Standard	30A	1/32"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-57	Strip	Neoprene	Standard	30A	1/32"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-38	Strip	Neoprene	Standard	30A	1/16"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-48	Strip	Neoprene	Standard	30A	1/16"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-58	Strip	Neoprene	Standard	30A	1/16"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-39	Strip	Neoprene	Standard	30A	3/32"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-49	Strip	Neoprene	Standard	30A	3/32"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-59	Strip	Neoprene	Standard	30A	3/32"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-40	Strip	Neoprene	Standard	30A	1/8"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-50	Strip	Neoprene	Standard	30A	1/8"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-60	Strip	Neoprene	Standard	30A	1/8"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-41	Strip	Neoprene	Standard	30A	3/16"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-51	Strip	Neoprene	Standard	30A	3/16"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-61	Strip	Neoprene	Standard	30A	3/16"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-42	Strip	Neoprene	Standard	30A	1/4"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-52	Strip	Neoprene	Standard	30A	1/4"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-62	Strip	Neoprene	Standard	30A	1/4"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-43	Strip	Neoprene	Standard	30A	3/8"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-53	Strip	Neoprene	Standard	30A	3/8"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-63	Strip	Neoprene	Standard	30A	3/8"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-44	Strip	Neoprene	Standard	30A	1/2"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-54	Strip	Neoprene	Standard	30A	1/2"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-64	Strip	Neoprene	Standard	30A	1/2"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-45	Strip	Neoprene	Standard	30A	3/4"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-55	Strip	Neoprene	Standard	30A	3/4"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-65	Strip	Neoprene	Standard	30A	3/4"	6"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-46	Strip	Neoprene	Standard	30A	1"	2"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N30-56	Strip	Neoprene	Standard	30A	1"	4"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BC 310
BULK-RS-N40-863	Strip	Neoprene	Standard	40A	1/32"	2"	36"	Black	Plain	Smooth	ASTM D2000 BC 407