


**Fabric-Reinforced High Strength Buna-N Rubber**

These sheets have a fabric insert and stand up to high stress and flex. They are often used as flange gaskets, diaphragm packing, and in other applications with heavy compression. Buna-N is ideal for oils, greases, fuels, and petroleum applications.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture	Specs Met
BULK-RS-HFR60-219	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	6"	6"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-23	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	12"	12"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-9	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	36"	12"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-235	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	36"	24"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-16	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	36"	36"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-220	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	6"	6"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-24	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	12"	12"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-10	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	36"	12"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-236	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	36"	24"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-17	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	36"	36"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-222	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	6"	6"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-26	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	12"	12"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-12	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	36"	12"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-237	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	36"	24"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-19	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	36"	36"	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-226	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	6"	6"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-51	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-44	Sheet	Buna-N	Fabric-Reinforced	60A	1/16"	36"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-227	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	6"	6"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-52	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-45	Sheet	Buna-N	Fabric-Reinforced	60A	1/8"	36"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-229	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	6"	6"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-54	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	12"	12"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-47	Sheet	Buna-N	Fabric-Reinforced	60A	1/4"	36"	36"	Black	Acrylic Adhesive	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-238	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	4 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-241	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	5 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-244	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	6 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-247	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	7 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-250	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	8 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-253	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	9 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-205	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	10 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-232	Roll	Buna-N	Fabric-Reinforced	60A	1/16"	36"	50 ft.	Black	Plain	Smooth	ASTM D2000 BF 610
BULK-RS-HFR60-239	Roll	Buna-N	Fabric-Reinforced	60A	1/8"	36"	4 ft.	Black	Plain	Smooth	ASTM D2000 BF 610