

JB-W with 2 row terminal blocks

RoHS2

Protection Color



Model designation

JB-W3□□□□

- Nil . . . Black
- C1 . . . Light gray
- BJ . . . Beige
- Nil . . . Oilproof
- E . . . Weatherproof
- Number of poles

Rated voltage Rated current Oilproof Weatherproof



Number of poles



Model			Rating	Applicable crimp terminal (mm)	Working temperature	Cable cross section	Number of poles	Terminal screw	Weight	Q'ty per package
Black	Light gray	Beige								
JB-W305/305E	JB-W305C1	JB-W305BJ/305EBJ	AC/DC 300V 15A	Max. 6.0 Min. 4.5 Min. φ3	-25 to +80°C	Max. 1.25mm ²	5P 7P 11P	M3×8 fall prevention terminal screw	100g 117g 170g	1 pc.

JB-W Slim type with 1 row terminal block

RoHS2

Protection Color



Model designation

JB-WS3□□□□

- Nil . . . Black
- C1 . . . Light gray
- BJ . . . Beige
- Nil . . . Oilproof
- E . . . Weatherproof
- Number of poles

Rated voltage Rated current Oilproof Weatherproof



Number of poles



Model			Rating	Applicable crimp terminal (mm)	Working temperature	Cable cross section	Number of poles	Terminal screw	Weight	Q'ty per package
Black	Light gray	Beige								
JB-WS303/303E	JB-WS303C1	JB-WS303BJ/303EBJ	AC/DC 300V 15A	Max. 6.0 Min. 4.5 Min. φ3	-25 to +80°C	Max. 1.25mm ²	3P 4P 7P	M3×8 fall prevention terminal screw	44g 65g 94g	10 pcs. 1 pc.

JB-W Slim type with 2 row terminal blocks

RoHS2

Protection Color



Model designation

JB-WST3□□□□

- Nil . . . Black
- BJ . . . Beige
- Nil . . . Oilproof
- E . . . Weatherproof
- Number of poles

Rated voltage Rated current Oilproof Weatherproof



Number of poles



Model		Rating	Applicable crimp terminal (mm)	Working temperature	Cable cross section	Number of poles	Terminal screw	Weight	Q'ty per package
Black	Beige								
JB-WST303/303E	JB-WST303BJ/303EBJ	AC/DC 300V 15A	Max. 6.0 Min. 4.5 Min. φ3	-25 to +80°C	Max. 1.25mm ²	3P 4P 6P	M3×8 fall prevention terminal screw	46g 63g 85g	1 pc.

JB-W Slim blank type

RoHS2

Protection Color




Model designation

JB-WSB028070□□

- Nil . . . Black
- BJ . . . Beige
- Nil . . . Oilproof
- E . . . Weatherproof

Oilproof Weatherproof



Model		Working temperature	Applicable crimp terminal (mm)	Weight	Q'ty per package
Black	Beige				
JB-WSB028070/028070E	JB-WSB028070BJ/028070EBJ	-25 to +80°C	φ 5-7	33g	1 pc.
JB-WSB034070/034070E	JB-WSB034070BJ/034070EBJ		φ 6-9	45g	
JB-WSB049070/049070E	JB-WSB049070BJ/049070EBJ		φ 6-9	58g	