


Abrasion Resistant Polyurethane

Polyurethane

Polyurethane has exceptional tensile strength, tear resistance, and shock absorption qualities. It is far stronger than comparable rubber materials and is often used for high-tension and high-wear applications.



Part Number	Shape	Material	Grade	Durometer	Thickness	Width	Length	Color	Backing Type	Texture
BULK-RS-P60-57	Strip	Polyurethane	High Strength	60A	1/16"	1/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-58	Strip	Polyurethane	High Strength	60A	1/16"	1/2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-59	Strip	Polyurethane	High Strength	60A	1/16"	3/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-60	Strip	Polyurethane	High Strength	60A	1/16"	1"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-64	Strip	Polyurethane	High Strength	60A	1/16"	2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-97	Strip	Polyurethane	High Strength	60A	1/8"	1/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-98	Strip	Polyurethane	High Strength	60A	1/8"	1/2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-99	Strip	Polyurethane	High Strength	60A	1/8"	3/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-100	Strip	Polyurethane	High Strength	60A	1/8"	1"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-104	Strip	Polyurethane	High Strength	60A	1/8"	2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-107	Strip	Polyurethane	High Strength	60A	3/16"	1/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-108	Strip	Polyurethane	High Strength	60A	3/16"	1/2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-109	Strip	Polyurethane	High Strength	60A	3/16"	3/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-110	Strip	Polyurethane	High Strength	60A	3/16"	1"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-114	Strip	Polyurethane	High Strength	60A	3/16"	2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-87	Strip	Polyurethane	High Strength	60A	1/4"	1/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-88	Strip	Polyurethane	High Strength	60A	1/4"	1/2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-89	Strip	Polyurethane	High Strength	60A	1/4"	3/4"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-90	Strip	Polyurethane	High Strength	60A	1/4"	1"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-94	Strip	Polyurethane	High Strength	60A	1/4"	2"	10 ft.	Amber	Plain	Smooth
BULK-RS-P60-205	Sheet	Polyurethane	High Strength	60A	1/16"	6"	6"	Amber	Plain	Smooth
BULK-RS-P60-23	Sheet	Polyurethane	High Strength	60A	1/16"	12"	12"	Amber	Plain	Smooth
BULK-RS-P60-9	Sheet	Polyurethane	High Strength	60A	1/16"	36"	12"	Amber	Plain	Smooth
BULK-RS-P60-252	Sheet	Polyurethane	High Strength	60A	1/16"	36"	24"	Amber	Plain	Smooth
BULK-RS-P60-16	Sheet	Polyurethane	High Strength	60A	1/16"	36"	36"	Amber	Plain	Smooth
BULK-RS-P60-206	Sheet	Polyurethane	High Strength	60A	1/8"	6"	6"	Amber	Plain	Smooth
BULK-RS-P60-24	Sheet	Polyurethane	High Strength	60A	1/8"	12"	12"	Amber	Plain	Smooth
BULK-RS-P60-10	Sheet	Polyurethane	High Strength	60A	1/8"	36"	12"	Amber	Plain	Smooth
BULK-RS-P60-218	Sheet	Polyurethane	High Strength	60A	1/8"	36"	24"	Amber	Plain	Smooth
BULK-RS-P60-17	Sheet	Polyurethane	High Strength	60A	1/8"	36"	36"	Amber	Plain	Smooth
BULK-RS-P60-207	Sheet	Polyurethane	High Strength	60A	3/16"	6"	6"	Amber	Plain	Smooth
BULK-RS-P60-25	Sheet	Polyurethane	High Strength	60A	3/16"	12"	12"	Amber	Plain	Smooth
BULK-RS-P60-11	Sheet	Polyurethane	High Strength	60A	3/16"	36"	12"	Amber	Plain	Smooth
BULK-RS-P60-219	Sheet	Polyurethane	High Strength	60A	3/16"	36"	24"	Amber	Plain	Smooth
BULK-RS-P60-18	Sheet	Polyurethane	High Strength	60A	3/16"	36"	36"	Amber	Plain	Smooth
BULK-RS-P60-208	Sheet	Polyurethane	High Strength	60A	1/4"	6"	6"	Amber	Plain	Smooth
BULK-RS-P60-26	Sheet	Polyurethane	High Strength	60A	1/4"	12"	12"	Amber	Plain	Smooth
BULK-RS-P60-12	Sheet	Polyurethane	High Strength	60A	1/4"	36"	12"	Amber	Plain	Smooth
BULK-RS-P60-220	Sheet	Polyurethane	High Strength	60A	1/4"	36"	24"	Amber	Plain	Smooth
BULK-RS-P60-19	Sheet	Polyurethane	High Strength	60A	1/4"	36"	36"	Amber	Plain	Smooth
BULK-RS-P60-210	Sheet	Polyurethane	High Strength	60A	1/2"	6"	6"	Amber	Plain	Smooth
BULK-RS-P60-28	Sheet	Polyurethane	High Strength	60A	1/2"	12"	12"	Amber	Plain	Smooth
BULK-RS-P60-14	Sheet	Polyurethane	High Strength	60A	1/2"	36"	12"	Amber	Plain	Smooth
BULK-RS-P60-221	Sheet	Polyurethane	High Strength	60A	1/2"	36"	24"	Amber	Plain	Smooth
BULK-RS-P60-21	Sheet	Polyurethane	High Strength	60A	1/2"	36"	36"	Amber	Plain	Smooth
BULK-RS-P60-212	Sheet	Polyurethane	High Strength	60A	1/16"	6"	6"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-51	Sheet	Polyurethane	High Strength	60A	1/16"	12"	12"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-37	Sheet	Polyurethane	High Strength	60A	1/16"	36"	12"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-44	Sheet	Polyurethane	High Strength	60A	1/16"	36"	36"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-213	Sheet	Polyurethane	High Strength	60A	1/8"	6"	6"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-52	Sheet	Polyurethane	High Strength	60A	1/8"	12"	12"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-38	Sheet	Polyurethane	High Strength	60A	1/8"	36"	12"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-45	Sheet	Polyurethane	High Strength	60A	1/8"	36"	36"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-214	Sheet	Polyurethane	High Strength	60A	3/16"	6"	6"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-53	Sheet	Polyurethane	High Strength	60A	3/16"	12"	12"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-39	Sheet	Polyurethane	High Strength	60A	3/16"	36"	12"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-46	Sheet	Polyurethane	High Strength	60A	3/16"	36"	36"	Amber	Acrylic Adhesive	Smooth
BULK-RS-P60-215	Sheet	Polyurethane	High Strength	60A	1/4"	6"	6"	Amber	Acrylic Adhesive	Smooth