

PB C6 188

PrecisionBit, Design C 6.3 (1/4")

- for spanner screws (Snake Eyes)
- everyday tool for all types of industry and trade screw applications, can be used manually and with machines
- compatible external hexagon in accordance with DIN ISO 1173, compatible with socket D 6.3
- precise, true-to-size tips, optimal fit in the screw heads
- color-coded by screw type so that you have the right bit, quickly at hand
- durability and hardness are optimally balanced thus ensuring an extremely long service life
- durable, special tool steel with attractive plasma coating for corrosion protection

PrecisionBit, forma C 6,3 (1/4")

- para tornillos Spanner (Snake Eyes)
- herr de uso diario para todos los trabajos de atornillado industrial y artesanal; uso manual o mecánico
- hexágono exterior compatible según DIN ISO 1173, apto para alojamiento D 6,3
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- codificación por colores según el tipo de tornillo, para tener rápidamente a mano la punta adecuada
- equilibrio óptimo de resistencia y dureza, vida útil extremadamente larga
- acero especial para herr. especial, duro y resistente; recubrimiento con plasma para protección antióxido



PB C6.188/4	4	3.3	39	12	10	7 610733 076901
PB C6.188/8	8	5	39	12	10	7 610733 076918
PB C6.188/10	10	6.2	39	12	10	7 610733 076925
PB C6.188/12	12	7.7	39	12	10	7 610733 070268

PB C6 189

PrecisionBit, Design C 6.3 (1/4")

- for Tri-Wing® screws
- everyday tool for all types of industry and trade screw applications, can be used manually and with machines
- compatible external hexagon in accordance with DIN ISO 1173, compatible with socket D 6.3
- precise, true-to-size tips, optimal fit in the screw heads
- color-coded by screw type so that you have the right bit, quickly at hand
- durability and hardness are optimally balanced thus ensuring an extremely long service life
- durable, special tool steel with attractive plasma coating for corrosion protection

PrecisionBit, forma C 6,3 (1/4")

- para tornillos Tri-Wing®
- herr de uso diario para todos los trabajos de atornillado industrial y artesanal; uso manual o mecánico
- hexágono exterior compatible según DIN ISO 1173, apto para alojamiento D 6,3
- punta precisa de dimensiones exactas, ajuste óptimo en los tornillos
- codificación por colores según el tipo de tornillo, para tener rápidamente a mano la punta adecuada
- equilibrio óptimo de resistencia y dureza, vida útil extremadamente larga
- acero especial para herr. especial, duro y resistente; recubrimiento con plasma para protección antióxido



PB C6.189/0	0	25	5.5	10	7 610733 206179
PB C6.189/1	1	25	5	10	7 610733 206186
PB C6.189/2	2	25	5	10	7 610733 206193
PB C6.189/3	3	25	5	10	7 610733 206209
PB C6.189/4	4	25	5	10	7 610733 206216
PB C6.189/5	5	25	5	10	7 610733 206223